

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0508917112](#)
Status: **Obsolete**
Description: Spade Tongue Terminal for 12 AWG, Closed Uninsulated Brazed Barrel, Stud Size 8 (M4), Oxygen-Free Copper, Length 17.80mm (.701")

Documents:
[Drawing \(PDF\)](#)

Agency Certification

CSA	LR95446
UL	E134962

General

Product Family	Ring and Spade Terminals
Series	50891
Crimp Quality Equipment	Yes
Mil-Spec	N/A
Product Name	Y (Spade)
Type	Spade

Physical

Barrel Type	Closed - Brazed
Insulation	None
Material - Plating Mating	Tin
Packaging Type	Bag
Stud Size	8 (M4)
Wire Size AWG	12
Wire Size mm²	2.63 - 4.60

Material Info

Reference - Drawing Numbers

Product Specification	PS-50891-001
Sales Drawing	SD-50891-001



Series

image - Reference only

EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[50891Series](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Japan

Description	Product #
Air Type Hand Crimper For JIS Terminal	0573439005
Hand Crimper For JIS Terminal	0572575000