

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [35747-0310](#)
Status: **Active**
Overview: [VersaBlade™](#)
Description: Crimp Terminal 35747, 18+18, 20+20 AWG

Documents:

Drawing (PDF)	Product Specification PS-35182-003 (PDF)
Product Specification PS-35150-001 (PDF)	Packaging Specification PK-35747-001 (PDF)
Product Specification PS-35180-002 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	35747
Application	Power
Crimp Quality Equipment	Yes
Overview	VersaBlade™
Product Name	VersaBlade™
UPC	800754378550


Physical

Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.333/g
Packaging Type	Reel
Plating min - Mating	0.813µm
Plating min - Termination	0.813µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	6.00mm max.
Wire Size AWG	18+18, 20+20
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Packaging Specification	PK-35747-001
Product Specification	PS-35150-001, PS-35180-002, PS-35182-003
Sales Drawing	SD-35747-002



EU RoHS

**ELV and RoHS
Compliant**

REACH SVHC

Not Reviewed

Low-Halogen Status

Low-Halogen

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[35747Series](#)

Application Tooling | FAQ

*Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.*

Global

Description	Product #
FineAdjust™	0638629200
Applicator	
Extraction Tool	0638132700
T2 Terminator Die	0638529200
Hand Crimp Tool for	0638190700
1.80mm-Wide Crimp Terminals	
Hand Crimp Tool for	0638196900
Industry standard 1.78mm Tab Terminals, 24-26 AWG Wire	

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

onlinecomponents.com