

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [88741-9400](#)
Status: **Active**
Overview: MicroCross™ DVI
Description: MicroCross™ DVI Digital Visual Interface, Shielded I/O Adapter, DVI-I-Analog/Digital Receptacle-DVI Digital Plug

Documents:
[Drawing \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	I/O Connectors
Series	88744
Application	Wire-to-Board
Comments	DVI-I-Analog/Digital Receptacle-DVI Digital Plug
Component Type	Adapter
Overview	MicroCross™ DVI
Product Name	MicroCross™DVI
Type	N/A
UPC	800754798341

Physical

Circuits (Loaded)	29
Circuits (maximum)	29
Color - Resin	Black, Natural
Durability (mating cycles max)	100
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze, Steel
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic, Polyester
Net Weight	46.000/g
Orientation	Vertical
PCB Retention	Yes
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.90mm, 2.54mm
Polarized to Mating Part	Yes
Surface Mount Compatible (SMC)	N/A
Temperature Range - Operating	-20°C to +85°C
Termination Interface: Style	N/A, Through Hole
Wire Size AWG	N/A


Electrical

Current - Maximum per Contact	3A
Shielded	Yes
Voltage - Maximum	40V

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-88741-015
---------------	--------------



EU RoHS

RoHS Compliant by Exemption
REACH SVHC
Not Reviewed
Low-Halogen Status
Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series
[88744Series](#)

Mates With
[74320 Receptacles](#)