

SKBI 64/B64

Order No.: 2263023

<http://eshop.phoenixcontact.de/phoenix/treeViewClick.do?UID=2263023>

Plug-in card block, Nominal current: 1 A, Number of positions: 64,
Pitch: 0 mm, Color: green

Commercial data

GTIN (EAN)	
sales group	E212
Pack	1 pcs.
Customs tariff	85369010
Catalog page information	Page 524 (CC-2009)

Product notes

WEEE/RoHS-compliant since:
05/15/2006



[http://
www.download.phoenixcontact.com](http://www.download.phoenixcontact.com)
Please note that the data given
here has been taken from the
online catalog. For comprehensive
information and data, please refer
to the user documentation. The
General Terms and Conditions of
Use apply to Internet downloads.

Technical data**Dimensions / positions**

Length	66 mm
Height	162 mm
Width	118 mm
Pitch	0 mm
Number of positions	64

Hole diameter	4.2 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

Technical data

Range of articles	SKBI 64
Connection in acc. with standard	EN-VDE
Nominal current I_N	1 A
Nominal voltage U_N	125 V (in acc. with DIN VDE 0110/Gr.B)
Stripping length	8 mm

Connection data

Conductor cross section solid min.	0.2 mm ²
Conductor cross section solid max.	4 mm ²
Conductor cross section stranded min.	0.2 mm ²
Conductor cross section stranded max.	2.5 mm ²
Conductor cross section AWG/kcmil min.	24
Conductor cross section AWG/kcmil max	12

Certificates / Approvals

Certification


GOST

Accessories


Item	Designation	Description
Assembly		
2263007	SF-SKBI 64	Snap foot, for horizontal or vertical mounting of the SKBI plug-in card blocks, on the NS 35/7.5 DIN rail

Diagrams/Drawings

Dimensioned drawing



Schematic diagram



Address

PHOENIX CONTACT Deutschland GmbH
Flachsmarktstr. 8
32825 Blomberg, Germany
Phone +49 5235 3 12000
Fax +49 5235 3 41200
<http://www.phoenixcontact.de>



© 2011 Phoenix Contact
Technical modifications reserved;