

4

3

2

1

THIS DRAWING IS UNPUBLISHED

RELEASED FOR PUBLICATION

APR ,1995.

© COPYRIGHT 2010 By -

ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD

IR

—

SEE SHEET 1

—

—

—

SCHNITT A—A

SECTION A—A

0.6 TYP

7.4

18.4 REF

11.02 REF

9.6 REF

④

②

③

①

550±4

A

11

A

4.8

NUR -2

(-2 ONLY)

7.4

②

UNGERADE POLZAHL(ODD)

2.43

②

GERADE POLZAHL(STRAIGHT)

POSITION IN TUBE

Lage in Verpackungshre

⑤

OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI

④

OBSOLETE

③

SIEHE TABELLE
SEE TABLE

②

MITTELLINIE DER STIFTLAISTE
CENTER LINE OF THE PIN ROW

①

AMPMODU II SMD—STIFTLAISTE SIEHE BLATT 1 VON 2.
AMPMODU II SMD—PIN ROW SEE SHEET 1 OF 2.

1-966 269-0	10	20
966 269-9	9	23
966 269-8	8	25
④ 966 269-7	7	29
④ 966 269-6	6	34
966 269-5	5	41
966 269-4	4	51
966 269-3	3	69
④ 966 269-2	2	108
BESTELL-NR. PART NO.	POLZ. PROREIHE POLZ. PER ROW	VERPACKUNGS-EINHEIT PACKING UNIT

OBSOLETE

⑤

S.TABELLE SEE TABLE	4	③	ADAPTER	PCT-GF	SCHWARZ / BLACK	4
	3	③	AMPMODU II STIFTL., SMD	①	①	3
	2	2	VERSCHL. STIFT / LOCKS PIN	PP	ROT	2
	1	1	VERPACKUNGSROHR / PACKING PIPE	ANTI-STATISCH	TRANSPAR.	1
BESTELL-NR. / PN	POS.	STÜCK / PIECE	BENENNUNG EINZELTEIL PART DESCRIPTION	WERKSTOFF MATERIAL	OBERFLÄCHE / FARBE SURFACE / COLOR	SI No

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

①

②

③

④

⑤

TOLERANCES UNLESS
OTHERWISE SPECIFIED:
TOL ± 0.2

0 PLC ± 0.2

1 PLC ±

2 PLC ±

3 PLC ± -

4 PLC ± -

ANGLES ±

FINISH

MATERIAL
SEE TABLE

FINISH
SEE TABLE

DWN
A.HO
23.03.95

CHK
M.SCHAARSCHMIDT
23.03.95

APVD
—

PRODUCT SPEC
108-18012

APPLICATION SPEC
—

WEIGHT
—

CUSTOMER DRAWING

STE

TE Connectivity

NAME
AMPMODU II PIN HEADER , SMD,
PACKED IN TUBE

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-966269

RESTRICTED TO
—

SCALE
2:1

SHEET
2 OF 2

REV
F

1470-19 (3/11)