




TECHNICAL SPECIFICATIONS:

I- MATERIAL: HOUSING: POLYESTER G.F. UL94V0
 COLOR : BLACK
 TERMINAL : PHOSPHOR BRONZE PLATED WITH
 0.00127-0.00152/.000050-.000060 GOLD
 IN CONTACT AREA , 0.00190/.000075 MIN
 PURE TIN IN TAIL AREA BOTH OVER
 0.00127/.000050 MIN NICKEL OVERALL
 SHIELD : BRASS PLATED WITH 0.0020/.000078
 MIN TIN




NOTES :

- 1- JACK FOR MATING WITH F.C.C. 68 PLUGS 95043 MOLEX SERIES.
- 2- PRODUCT SPECIFICATION: MOLEX PS-85505.
- 3- APPLICATION SPECIFICATION: MOLEX AS-95001.
- 4- PACKAGING SPECIFICATION: MOLEX PK-95123.
- 5- P.C. BOARD THICKNESS (SEE CHART) DIM A
- 6- EXCEEDS CATEGORY 5E PERFORMANCE.



PART NUMBER	TOOLED	PCB THICKNESS
85508-0001	YES	1.57/.062
85508-0002	NO	1.20/.047



ENTER DESCRIPTION		QUALITY SYMBOLS		GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE		DESIGN UNITS		THIRD ANGLE PROJECTION	
EC NO: MG2005-0139		2004/10/15		mm		MM ONLY		5:1		METRIC		⊙ □	
DRWN:KNOLLER		2004/10/15		4 PLACES ± --- ± ---		DRAWN BY		DATE		TITLE		HIGH SPEED MODULAR JACK	
CHKD:FCARABET		2004/10/15		3 PLACES ± --- ± .010		HB		99/07/07		TOP ENTRY 8 CKTS		THROUGH HOLE VERSION	
APPR:KNOLLER		2004/10/15		2 PLACES ± 0.25 ± .014		CHECKED BY		DATE		MOLEX INCORPORATED		SHEET NO.	
				1 PLACE ± 0.35 ± ---		APPROVED BY		DATE		SD-85508-001		1 OF 1	
				ANGULAR ± 2 °		MATERIAL NO.		DOCUMENT NO.					
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SIZE		SEE CHART					
						A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					