

1

2

3

4

A

A

B

B

C

C

D

D

Part Number

CONFIGURATION

POS	12	11	10	9	8	7	6	5	4	3	2	1
D	-	-	-	-	-	-	-	-	-	-	-	-
C	-	-	-	-	-	-	-	-	-	-	-	-
B	-	-	-	-	-	-	-	-	-	-	-	-
A	-	-	-	-	-	-	-	-	-	-	-	-

10126492-X01
OR
10126492-X01LF

Part Number


CONFIGURATION

POS	12	11	10	9	8	7	6	5	4	3	2	1
D	-	-	-	-	-	-	-	-	-	-	-	-
C	-	-	-	-	-	-	-	-	-	-	-	-
B	-	-	-	-	-	-	-	-	-	-	-	-
A	-	-	-	-	-	-	-	-	-	-	-	-

10126492-X02
OR
10126492-X02LF



SELECTIVE CONTACT LOADING

NOTE: " - " POSITION LOADED



GENERAL CHARACTERISTICS AND ROHS INFORMATIONS:

SEE GS-12-447

NOTE-1: MORE INFORMATIONS FOR PCB LAYOUT
SEE GS-12-447

P/N 10126492-XY/XYLF	
DASH NUMBER:	PERFORMANCE LEVEL
-1YY/1YYLF	TELCORDIA CO
-2YY/2YYLF	CUSTOMER SPECIAL




TABLE 1

PLATED THRU HOLE REQUIREMENTS

HOLE DIAMETER AFTER PLATING	0.65-0.80
DRILLED HOLE	0.81-0.86 (0.85 DRILL)
COPPER PLATING	0.025 - 0.05
SnPb PLATING	0.005-0.015

LAYOUT FOR P.C.B

scale : 2.0



Copyright FCI

rev	ecn no	dr	date
A	NEW RELEASE	QinDF	2013-11-04
B	ELX-DC-19619	MIC	2014-12-03
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302		tolerance std ISO 406 ISO 1101		projection 		 mm			
			TOLERANCES UNLESS OTHERWISE SPECIFIED									
Dr	Michael Song	2014/12/03	ANGULAR	LINEAR	0.X	±0.30	size	A3	Scale	3		
Eng	Michael Song	2014/12/03			0.XX	±0.15						
Chr	Zhen Luo	2014/12/03			0.XXX	±0.10	ECN		ELX-DG-19619			
Appr	Collins Lu	2014/12/03	Product family		METRAL		Spec ref		-			
		title				METRAL FEM. 4 ROW SL STRAIGHT PRESS FIT				dwg no 10126492		Rev B
						PCB THICKNESS: 2.4 mm MINIMUM						
		catalog no				-		CUSTOMER		sheet 1 of 1		

REV F - 2006-04-17

PDS: Rev :B

STATUS:Released

Printed: Dec 04, 2014