

Rubber Grommet KG-Type




Characteristic

Installation can be made with a single touch and it is effective on preventing wire disconnection.

Application


Controller devices / Telecommunication devices / Electric appliances, etc.



Model No.	Material	Hardness	Color
KG	EPDM	50°±5°	Black

Model No.	A	B	C	D	E	F	Net Weight (g)	Code No.
KG-74	7	5	3	4	1	R1	0.1	5223
KG-742	7	5	3	5	2	R1	0.1	5224
KG-95	9	7	3	5.5	0.8	R1.5	0.3	5225
KG-115	11	8	5	5	1	R1.5	0.4	5226
KG-135	13	8	5.5	5	1	R1.5	0.5	5227
KG-16	16	12	9	6.5	1.5	R3	0.6	5229

Rubber Grommet MG-Type



For MG-9

Characteristic

It has a dustproof function other than wire disconnection preventing effect that ordinary grommets have.

Application

Computers / Measuring instruments / Telecommunication devices / Electric appliances, etc.

Model No.	Material	Hardness	Thickness of Membrane (mm)	Color
MG	EPDM	50°±5°	approx.0.5	Black

Model No.	A	A1	B	C	D	D1	D2	E	Net Weight (g)	Code No.
MG-1	23	20	16	11	8.1	3.5	2	1.6	2.6	5601
MG-2	25	22	18	13	8.8			2.3	3.0	5602
MG-3	27	24	20	15	9.1	4	2.5	1.6	4.0	5603
MG-4	29	26	22	17	9.8			2.3	4.6	5604
MG-5	31	28	24	19	11.3	5	3	6.1	5.6	5605
MG-6	35	31	26		12.2			3.2	8.2	5606
MG-7	37	33	28	21	11.8			2.3	8.5	5607
MG-8	39	35	30	23	12.7			3.2	9.5	5608
MG-9	35			25	8	3	2	5.0	5609	
MG-10	41	37	32		11.8	5	2.3	9.7	5610	
MG-11	43	39	34	27	12.7		3.2	11.0	5611	
MG-12	45	42	36	28	13.8	6	4	2.3	14.5	5612
MG-13	48	44	38	30	14.7			3.2	17.5	5613
MG-14	16	13	9	4.5	8.5	3.5	2	2.3	1.3	5614
MG-15	19	16	12	7	6.3	2.5	1.5	1.6	1.5	5615
MG-16	21	18	14	9	8	3	2	2.3	2.0	5616
MG-17	52	48	42	34	14.7	6	4	3.2	19.5	5617