






NOTES:

1. SOLDER TERMINAL ARRANGEMENT: 4,5.
2. CONTACT RATING 0.25 AMP, 30 WATTS MAX,
AC, NON - INDUCTIVE LOAD.
3. DIELECTRIC STRENGTH - 500 VOLTS, RMS. MIN.
4. SWITCH MOUNTS IN PANELS 0.047 TO 0.281 THICK.
POSITION 1: 0.047 - 0.094
POSITION 2: 0.094 - 0.141
POSITION 3: 0.141 - 0.188
POSITION 4: 0.188 - 0.234
POSITION 5: 0.234 - 0.281
5. MATERIALS:
HOUSING: THERMOPLASTIC, CHARCOAL GRAY
PUSHBUTTON: THERMOPLASTIC, COLOR (SEE CHART)
MOUNTING CLIP: COPPER ALLOY
CONTACT SPRING, INTEGRAL: COPPER ALLOY, SILVER PLATED
TERMINALS: COPPER ALLOY, SILVER PLATED
ACTUATOR: THERMOPLASTIC, BEIGE
SPRING: MUSIC WIRE, TINNED
RETAINER PLATE: PAPER EPOXY LAMINATE
6. THESE PRODUCTS ARE RoHS COMPLIANT.

PART NUMBER	PUSHBUTTON COLOR
BXR011	RED
BXR021	BLACK
BXR031	GREEN
BXR051	WHITE



SCHEMATIC
1-A



CUSTOMER DRAWING

					★ STAR SYMBOL DENOTES CRITICAL DIMENSION	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.				
					UNLESS OTHERWISE SPECIFIED	SIZE	WIDTH	MULT	LBS/M	TEMPER
					1. ALL DIMENSIONS IN INCHES - TWO PLACE DECIMALS ±0.01 - THREE PLACE DECIMALS ±0.005 - ANGLES ±1° - ALL DIA. CONCENTRIC WITHIN 0.005 T.I.R.	FINISH SPEC No.		MATERIAL SPEC No.		
					2. FEATURES ON THE SAME CENTERLINE MUST BE ALIGNED WITHIN ±0.002	FIRST USED ON		SCALE 3:1		Switchcraft®
					3. REMOVE ALL BURRS	DATE DRAWN	BY	CHKD	APVD	
A	27357	9-12-14	TO	TJK		8-25-14	TO	TO 8-25-14	TJK 8-25-14	
REV	ECO NUMBER	DATE	BY	APVD		NAME		PART No.		REV
REVISIONS					DO NOT SCALE DRAWING	BXR SWITCH, MOMENTARY SOLDER TERMINALS, RoHS		BXR0_1 SERIES		A