



## Straight Blade Configurations, 15 & 20 Amp

Click on blue part numbers to download detailed Spec Sheets (MS Word format).

| Amps | Poles/<br>Wires | Volt. | NEMA<br>Config. | AC<br>HP<br>Rating | Appl.<br>Envir.    | Connector                   | Plug                        | Single<br>Receptacle | Duplex<br>Receptacle   | Flanged<br>Inlet      | Flanged<br>Outlet     | Dust<br>Resistant Inlet | Dust<br>Resistant<br>Outlet |
|------|-----------------|-------|-----------------|--------------------|--------------------|-----------------------------|-----------------------------|----------------------|------------------------|-----------------------|-----------------------|-------------------------|-----------------------------|
| 15A  | 2P<br>3W        | 125V  |                 | 0.5                | Spec.<br>Grade     | <a href="#">5269*</a>       | <a href="#">5266*</a>       | 5251                 | <a href="#">5252</a>   | <a href="#">5278*</a> | <a href="#">5279*</a> | <a href="#">5278DRI</a> | 5279DRO                     |
|      |                 |       |                 |                    | Corr.<br>Resistant | 5269CRS                     | 5266CRS                     | 5251CRS              | --                     | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    | All<br>Black       | 5269BL*                     | 5266BL*                     | --                   | --                     | 5278BL                | 5279BL                | --                      | --                          |
|      |                 |       |                 |                    | Hospital<br>Grade  | <a href="#">8219</a>        | 8215                        | 8210                 | 8200                   | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    |                    | 8219T<br>(Trans-<br>parent) | 8215T<br>(Trans-<br>parent) | --                   | --                     | --                    | --                    | --                      | --                          |
|      | 2P<br>3W        | 250V  |                 | 2                  | Isolated<br>Ground | --                          | 5266IG                      | 5261IG               | <a href="#">5262IG</a> | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    | Spec.<br>Grade     | <a href="#">5669*</a>       | <a href="#">5666*</a>       | <a href="#">5651</a> | 5662                   | <a href="#">5678*</a> | <a href="#">5679*</a> | <a href="#">5678DRI</a> | 5679DRO                     |
|      |                 |       |                 |                    | Hospital<br>Grade  | 8619                        | 8615                        | --                   | 8600                   | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    |                    | 8619T<br>(Trans-<br>parent) | 8615T<br>(Trans-<br>parent) | --                   | --                     | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    |                    |                             |                             |                      |                        |                       |                       |                         |                             |
| 20A  | 2P<br>3W        | 125V  |                 | 1                  | Spec.<br>Grade     | <a href="#">5369*</a>       | <a href="#">5366*</a>       | 5351                 | 5352                   | <a href="#">5378*</a> | <a href="#">5379*</a> | <a href="#">5378DRI</a> | 5379DRO                     |
|      |                 |       |                 |                    | Corr.<br>Resistant | 5369CRS                     | 5366CRS                     | 5351CRS              | 5352CRS                | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    | All<br>Black       | 5369BL*                     | 5366BL*                     | --                   | --                     | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    | Hospital<br>Grade  | 8319                        | 8315                        | 8310                 | 8300                   | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    |                    | 8319T<br>(Trans-<br>parent) | 8315T<br>(Trans-<br>parent) | --                   | --                     | --                    | --                    | --                      | --                          |
|      | 2P<br>3W        | 250V  |                 | 2                  | Isolated<br>Ground | --                          | 5366IG                      | 5351IG               | 5352IG                 | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    | Spec.<br>Grade     | <a href="#">5469*</a>       | <a href="#">5466*</a>       | 5461                 | 5462                   | <a href="#">5478*</a> | <a href="#">5479*</a> | <a href="#">5478DRI</a> | 5479DRO                     |
|      |                 |       |                 |                    | Hospital           | 8419                        | 8415                        | --                   | 8400                   | --                    | --                    | --                      | --                          |
|      |                 |       |                 |                    |                    |                             |                             |                      |                        |                       |                       |                         |                             |
|      |                 |       |                 |                    |                    |                             |                             |                      |                        |                       |                       |                         |                             |

|  |  |  |  |  |       |                             |                             |    |    |    |    |    |    |
|--|--|--|--|--|-------|-----------------------------|-----------------------------|----|----|----|----|----|----|
|  |  |  |  |  | Grade | 8419T<br>(Trans-<br>parent) | 8415T<br>(Trans-<br>parent) | -- | -- | -- | -- | -- | -- |
|--|--|--|--|--|-------|-----------------------------|-----------------------------|----|----|----|----|----|----|

\*Also available with .CN option: Combination Slot & Robertson Head Screws.

Also available: Complete 15A Right Angle Plugs and 15RA (Right Angle) Adapter for plugs and connectors. See [Right Angle Plugs & Adapter](#).

## For Specifications & Dimensional Drawings

You can also download Adobe® Acrobat® files with Agency Listings, Mechanical and Electrical data, and Material specifications, with 3-dimensional drawings of Marinco SWD's Straight Blade Configurations, 15Amp & 20 Amp, by clicking [straight.pdf](#). If you don't have Acrobat® Reader®, you can download it free from [Adobe](#).

[Overview](#) of Product Features / [Find](#) By Amperage or Product Group  
[Cross Reference](#) / What's [New](#) / Free Product [Literature](#) /  
 Manufacturer [Representatives](#) / Marinco [SWD Home](#)  
 Guest Industrial [Battery Chargers](#) / Marinco [Corporate](#) Home Page  
 NEW! [Distributor Locator](#)



2655 Napa Valley Corporate Drive  
 Napa, California 94558 USA  
 Tel: 800-767-8541 or 707-226-8600  
 Fax: 707-226-9670  
 Email: [industrialinfo@marinco.com](mailto:industrialinfo@marinco.com)

©2003 Marinco. Marinco®, ConnectPro® and Perma-Lock(tm) are trademarks of Marinco.  
 All other trademarks are property of their respective owners.