





MATERIAL NUMBER	OLD PART NUMBER
130034-0007	8A5000-32DN



FEMALE FACE VIEW

P1	
1	SILVER (DRAIN)
2	RED (V+)
3	BLACK (V-)
4	WHITE (CAN_H)
5	BLUE (CAN_L)

COLOR-CODING CHART



VOLTAGE RATING	36VAC/VDC
AMPERAGE RATING	4 AMPS
PROTECTION	IP67
OPERATING TEMPERATURE	-25°C TO 90°C
CSA CERTIFICATIONS	CSA CERTIFIED, FILE NO. LR6837

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON	BLACK
2	CONTACTS	COPPER ALLOY	SILVER PLATED
3	O-RING	NITRILE	RED
4	COUPLING NUT	BRASS	NICKEL PLATED
5	MOLDED BODY	NYLON	BLACK
6	GROMMET	NITRILE	BLACK
7	CORD GRIP BODY	NYLON	BLACK

RLSD DRAWING EC NO: WNA2009-0624 DRWN: BWOODMAN 3/25/09 CH'KD: JM APPR: JFMURPHY 2009/04/01 A	DESCRIPTION REV	QUALITY SYMBOL ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)			DIMENSION STYLE IN/MM		SCALE ----	DESIGN UNITS ----	THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY BW	DATE 2009/03/26	TITLE M12 5P FEMALE ATTACHABLE DEVICENET COLOR CODED ----				
			4 PLACES	±---	±---	CHECKED BY LH	DATE 2009/03/26					
			3 PLACES	±----	±----	APPROVED BY DATE -----		molex MOLEX INCORPORATED				
			2 PLACES	±----	±.01							
			1 PLACE	±0.3	±----	MATERIAL NO. SEE CHART						
			ANGULAR ±----°								DOCUMENT NO. SD-130034-001	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SHEET NO. 1 OF 1									
			SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION								