

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0395116402](#)  
**Status:** **Obsolete**  
**Description:** 3.81mm (.150") Pitch Eurostyle™ Vertical PCB Header, with Reverse Imprinting, Green Housing, 2 Circuits

**Documents:**  
[Drawing \(PDF\)](#)

**General**

Product Family	Terminal Blocks
Series	<a href="#">39511</a>
Application	Wire-to-Board
Comments	with Reverse Imprinting
Component Type	PCB Header
Product Name	ESE, Eurostyle™ Pluggable
Type	Euro Block

**Physical**

Circuits (Loaded)	2
Entry Angle	N/A
Lock to Mating Part	None
Number of Rows	1
Orientation	Vertical
PC Tail Length	3.50mm (.138")
PCB Thickness - Recommended	2.50mm (.098")
Panel Mount	No
Pitch - Mating Interface	3.81mm (.150")
Pitch - Termination Interface	3.81mm (.150")
Polarized to Mating Part	Yes
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Wire Size AWG	N/A


**Electrical**

Current - Maximum per Contact	8A
Voltage - Maximum	300V

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-39500-001
Sales Drawing	SD-39501-002, SD-39511-001



**EU RoHS**

**ELV and RoHS  
Compliant**  
**REACH SVHC**  
 Not Reviewed  
**Low-Halogen Status**  
 Not Reviewed

**China RoHS**



**Need more information on product  
environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

**Search Parts in this Series**

[39511Series](#)

**Mates With**

Most 3.81mm (.150") Pitch Industry Standard Plugs, [39513](#) Vertical Plug, [39510](#) Horizontal Plug