





.165"(4.2mm) Power Connector System

9360-xxP Series Right Angle Header

inches
mm

- Available in 2 to 24 circuits
- .045"(1.14mm) square wire pin
- Material: UL 94V-2 nylon 66
- Positive housing locks
- Mates with ALEX 9357 series housing
- Dielectric withstanding voltage: 1500V AC/minute
- Ambient temperature range: -40 °C ~ 105 °C
- Recommended P.C.B. thickness: 1.78mm max.
- UL file No.: E114003
- CSA file No.: LR86545










$$A = (\text{Number of circuits} / 2 - 1) \times 4.2$$

PCB LAYOUT: COMPONENT SIDE

Circuits	Dimensional Information	Circuits	Dimensional Information
2	9360-02P	4	9360-04P
6	9360-06P	8	9360-08P



.165"(4.2mm) Power Connector System

Circuits	Dimensional Information	Circuits	Dimensional Information
10	9360-10P 	12	9360-12P 
14	9360-14P 	16	9360-16P 
18	9360-18P 	20	9360-20P 
22	9360-22P 	24	9360-24P 