







4

3

2

第三角法 (THIRD ANGLE PROJECTION)

断面 C-C
(SECT.)断面 D-D
(SECT.)断面 B-B
(SECT.)断面 A-A
(SECT.)0.5 MAX
CUT-OFF TAB

- 注: 1. 通用規格
製品規格 108-5302
取付通用規格 114-5142
2. 取扱説明書 IS-503T

- NOTES: 1. APPLICABLE SPEC.
PRODUCT SPEC. 108-5302
APPLICATION SPEC. 114-5142
2. INSTRUCTION SHEET IS-503T

	NYE 製 : 502H-20-UV (NYE : 502H-20-UV ル)カチ才化処理 (APPLIED LUBRICANT OIL)	錫めき溶黄銅 (PRE TINNED BRASS)	175149-3
175153-2		錫めき溶黄銅 (PRE TINNED BRASS)	175149-2
175153-1		錫めき溶銅合金 (PRE TINNED COPPER ALLOY)	175149-1
パラ状端子型番 (L.P. P/N)	仕 上 (FINISH)	材 料 (MATERIAL)	型 番 (P/N)

		仕様 (NAME) (TAB CONTACT AMP. UNIVERSAL POWER CONN.) 77-コネクタ, アンブユニバーサルパワーコネクタ	
		仕様 (SPEC.) (WIRE RANGE) 0.12-0.35mm (AWG #26-#22) 仕様 (SPEC.) (INSULATION DIA) 1.2 ~ 2 mm	
仕様 (SPEC.) (MATERIAL) 表参照 仕様 (SPEC.) (FINISH) 表参照		仕様 (SPEC.) (SIZE) 1PC=±0.2 仕様 (SPEC.) (SIZE) 2PC=±0.3	
仕様 (SPEC.) (LOC) B J 仕様 (SPEC.) (REV) 5-1		仕様 (SPEC.) (NO.) C-175149 仕様 (SPEC.) (SHEET) C2	

C2 REV ECR M-006821	DR	TM	9/14
C1 REVISED PER ECO-11-005030	RK	HMR	2/14
LTR	2E (REVISION RECORD)	DR	CHK. DATE

DR: AM P/N: 175149
CHK: 2/14/14
DATE: 2/14/14

FIG. 11 DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DATE