

[illegible]

PANDUIT PART No.	REC'M. SCREW FASTENER	WEIGHT LBS./100 (g)/PCS.
FCM3.25-A	N/A	3.26 (1480)
FCM3.25-S6	#6 (M3) FL.HD. OR BUTTON HD.	3.04 (1380)

NO WARRANTY EXPRESSED OR IMPLIED, IS MADE BY PANDUIT WITH RESPECT TO ADHESIVE BOND PERFORMANCE. AMONG OTHER THINGS, THE CONDITIONS UNDER WHICH THESE MOUNTS MAY BE APPLIED AND/OR THE SURFACE TO WHICH THEY MAY BE APPLIED ARE BEYOND PANDUIT'S CONTROL.

ADHESIVE TAPE: PRESSURE SENSITIVE FOAM .040 (1.02) THICK
WITH RUBBER ADHESIVE AND PROTECTIVE LINER. MOUNT
IS DESIGNED TO SUPPORT 1.5 lbs. (680g) MAXIMUM WEIGHT
ON A CLEAN, DRY, SMOOTH, GREASE-FREE SURFACE.

SCALE: 3/4 0.60
(15.2)

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
2. TO APPLY MOUNT: a) REMOVE PROTECTIVE LINER; b) PLACE IN DESIRED LOCATION; c) APPLY PRESSURE TO TOP OF MOUNT.

(DIMENSIONS IN PARENTHESES ARE IN METRIC.)

[illegible]

G00239JE_PB_FCM3.25_00

PANDUIT

CORP.

TINLEY PARK, ILLINOIS

3.25 INCH FLAT CABLE MOUNT
FCM3.25

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± N/A (.XXX) ± N/A
(.XX) ± .020(.5) ANGLES ± 5°

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
LGG

	MAT'L:
--	--------

	SCALE
--	-------

FULL

DATE	7/18/02
------	---------

NYLON 6/6

DRAWING NO.

GB0239JE

DWG
A
SIZE

R	7-18-02	LGG		INITIAL RELEASE-REPLACED G-00173	GB0239JE	1				
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		