



LOC	DIST	P	F	REVISIONS			
				ZONE	LTR	DESCRIPTION	DATE
BD	48				F	REDRAWN	6/22/90
					G	OBS 1-8 PER ECN BD6177	06/19/92
					H	OBS -14 PER EC 0020-1534-93	04/14/94
					J	REV PER EC 0020-309-95	05/04/95
					K	REV PER EC 0020-881-95	25 AUG 95
					L	REV PER EC 0U1D-83-00	28 MAR 00

OPENING FOR CABLE
(SEE TABLE FOR DIA)



SIZE IDENTIFICATION LETTER
MOLDED IN APPROXIMATE AREA
SHOWN, SEE TABLE


#4-40 FILLISTER HEAD
STEEL SCREW & HEX NUT
ZINC PLATED
(2 EACH REQ'D)



TEXTURED
FINISH

AMP LOGO ON -1,-2,-3,
-7,-8,-9,1-3,1-4

.620
±.015



CABLE CLAMP (QTY:2)
MAT'L:ZINC ALLOY, PLATED NICKEL
OVER COPPER

.620
±.015

#4-40 FILLISTER HD SCREW
MAT'L: STEEL, ZINC PLATED ①
QTY:2

OBSOLETE	BULK PACKED AS SHOWN		.375	2-745172-5
			.300	2-745172-4
			.225	2-745172-3
	BULK PACKED 3		.375	2-745172-2
			.300	2-745172-1
			.225	2-745172-0
OBSOLETE	BULK PACKED 2		.375	1-745172-9
		E	.300	1-745172-8
OBSOLETE			.225	1-745172-7
	BULK PACKED AS SHOWN		.430	1-745172-6
	BULK PACKED 3		.430	1-745172-5
	3	K	.430	1-745172-4
	AS SHOWN	K	.430	1-745172-3
OBSOLETE	3	B	.225	745172-9
			.300	745172-8
			.375	745172-7
	AS SHOWN	B	.225	745172-3
		E	.300	745172-2
		H	.375	745172-1
	REMARKS	NECK IDENT	CABLE DIA	PART NO.

1. PARTS PACKAGED UNASSEMBLED.

② SUPPLIED WITHOUT MTG SCREWS ① & LOGO.

③ SUPPLIED WITHOUT MTG SCREWS ①.

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN INCHES TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± .005 ANGLES ± -	DR 6/22/90 A.STAUB BG	AMP AMP INCORPORATED Harrisburg, Pa. 17105		
	CHK 9/10/90 J.MCCLINTON			
MATERIAL SEE CALLOUTS	APPD 9/11/90 BOB TAYLOR	NAME CABLE CLAMP KIT, UNASSEMBLED, SIZE 2, 15 POSITION, 180°, AMPLIMITE™		
	APPD 9/11/90 J.ASSINI			
FINISH SEE CALLOUTS	PRODUCT SPEC -	SIZE C	FSCM NO 00779	DRAWING NO 745172
	APPLICATION SPEC -			
	WEIGHT -	SCALE 1:1	SHEET 1 OF 1	