



Type B Liquidtight Tubing & Fittings

T&B Catalog Number:

LTC050GY

78621088076

UPC Number:

Status:

Active

Description:

1/2 in. gray non-metallic Type B commercial grade liquidtight conduit.

Features

Fast installation, even in tight or cramped spaces.

Smooth inner diameter allows easy wire pulling.

Smooth outer jacket uses material approved for outdoor use, is sunlight resistant and oil resistant.

Lightweight and liquidtight.

Application

UL Listed for direct burial

General

Material	PVC
Color	Gray
Working Temperatures	-18 C to +105 C

Dimension Information

Size (inches)	1/2
I.D. - Minimum (inches)	0.622
I.D. - Maximum (inches)	0.642
O.D. - Minimum (inches)	0.82
O.D. - Maximum (inches)	0.84

Packaging

T&B Order Multiple	100
Package in Units	100
T&B Sold in UOM	Feet
T&B Weight Per UOM	14.31 lbs. per 100

Application Support

MSDS Number	msds-0023-tb2
Guide to Nonmetallic Conduit Applications	Available on Website
XTRAFLEX System Specifications	Available on Website

Certifications

RoHS Compliance	Yes
-----------------	-----

Certifications



File Nbr:

E 95745

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com