


1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERMINAL NUMBERS FOR REF. ONLY
4. CONTACT RATING: 0.1A @ 30VDC
5. TRAVEL: FULL = 2.5±0.3
6. OPERATING FORCE: 250± 100gf
7. ELECTRICAL LIFE: 10,000 CYCLES
8. ▲ DENOTES CRITICAL PARAMETER
9. CONTACT MATERIAL: SILVER
10. CONTACT RESISTANCE 50m OHM MAX.
11. OPERATING TEMPERATURE: -20c TO +70c
12. INSULATION RESISTANCE: 100M OHMS MIN.
13. LED COLOR: GREEN
14. 2002/95/EC (RoHS) COMPLIANT AND HALOGEN



B	19554	DIM CHANGES & UPDATE	12/30/10	BG1
14. 2002/95/EC (RoHS) COMPLIANT AND HALOGEN FREE				

1554	DATE	1/20/10	rc	DATE	1/20/2010	DR	rc	DWG	B401015	REV	B
A	18806	New-Release	rc	TITLE TL22050ABPGB							
REV	PCR NO	DESCRIPTION	DATE	BY	SCALE 2:1						
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED											