

SD SERIES

RELAY SOCKETS



DESCRIPTION

12 and 14 Pin Heavy Duty Sockets

ELECTRICAL RATING

- SD12-PC - 600 Volts, 10 Amps
- SD14-PC - 300 Volts, 10 Amps

CONSTRUCTION

- Contacts** • Brass, Nickel Plated
- Screws** • Pressure Clamp, 6 - 32 x 5/16" Steel, Zinc plated, Wire Range #12 - #22 Solid or Stranded
- Molding** • Break Resistant Thermoplastic

AGENCY APPROVALS

- UL recognized, File No. E60008
- CSA certified, File No. LR29513



ORDERING CODE

PART NO.

SD12-PC
SD14-PC

DESCRIPTION

12 Pin (Fig. 1)
14 Pin (Fig. 2)

TERMINAL TYPE

Pressure Clamp Screws
Pressure Clamp Screws



CUSTOM CONNECTOR

Fig. 1




Fig. 2

