

LOC		DIST		REVISIONS					
GP		00		P	LTR	DESCRIPTION	DATE	DWN	APVD
			H1	REVISED PER ECO-11-005033			23MAR11	RK	HMR

- 1

CONTACTS DESIGNED FOR 26 & 28 AWG STRANDED OR 26, 28, & 30 AWG SOLID WIRE.
- 2

AMP TRADEMARK LOCATED IN APPROX AREA SHOWN.
- 3

STANDOFFS: POS 10 (2) STANDOFFS AS SHOWN.
14-16 (3) STANDOFFS, (1) CENTERED BETWEEN (2) SHOWN
20-26 (4) (2)
30 (5) (3)
34 (6) (4)
40-44 (7) (5)
50 (8) (6)
60 (9) (7)
64 (10) (8)





- 4

.000100-.000200 BRIGHT TIN
LEAD, ALL OVER .000050 NICKEL.
- 5

HEIGHT AFTER TERMINATION IS .253 REF.
- 6

.000005 MIN GOLD ON RIBBON CABLE TERMINATION AREA
.000100-.000200 MIN MATTE TIN ON SOLDER TAILS, ALL OVER
.000050 MIN NICKEL.
- 7

MOLDED PARTS, 94V-0 RATED THERMOPLASTIC, COLOR: BLACK.
CONTACTS: PHOS BRONZE.



	6	2.100	21	2.380	2.100	2.150	43	44	2-746610-6
	6	3.100	31	3.380	3.100	3.150	63	64	2-746610-5
	6	2.900	29	3.180	2.900	2.950	59	60	2-746610-4
	6	1.100	11	1.380	1.100	1.150	23	24	2-746610-3
	6	.600	6	.880	.600	.650	13	14	2-746610-2
	6	.400	4	.680	.400	.450	9	10	2-746610-1
	6	2.400	24	2.680	2.400	2.450	49	50	2-746610-0
	6	1.900	19	2.180	1.900	1.950	39	40	2-746610-9
	6	1.600	16	1.880	1.600	1.650	33	34	2-746610-8
	6	1.400	14	1.680	1.400	1.450	29	30	2-746610-7
	6	1.200	12	1.480	1.200	1.250	25	26	2-746610-6
	6	.900	9	1.180	.900	.950	19	20	2-746610-5
	6	.700	7	.980	.700	.750	15	16	2-746610-4
OBSOLETE	4	2.100	21	2.380	2.100	2.150	43	44	1-746610-3
OBSOLETE	4	3.100	31	3.380	3.100	3.150	63	64	1-746610-2
OBSOLETE	4	2.900	29	3.180	2.900	2.950	59	60	1-746610-1
OBSOLETE	4	2.400	24	2.680	2.400	2.450	49	50	1-746610-0
	4	1.900	19	2.180	1.900	1.950	39	40	1-746610-9
	4	1.600	16	1.880	1.600	1.650	33	34	1-746610-8
OBSOLETE	4	1.400	14	1.680	1.400	1.450	29	30	1-746610-7
	4	1.200	12	1.480	1.200	1.250	25	26	1-746610-6
OBSOLETE	4	1.100	11	1.380	1.100	1.150	23	24	1-746610-5
	4	.900	9	1.180	.900	.950	19	20	1-746610-4
	4	.700	7	.980	.700	.750	15	16	1-746610-3
	4	.600	6	.880	.600	.650	13	14	1-746610-2
	4	.400	4	.680	.400	.450	9	10	1-746610-1
CONTACT FINISH	F	E	D	C	B	A	NO OF POSN	PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN L. VARELA - 11-29-86	TE Connectivity	
		CHK C. ROHDE - 11-29-04		
DIMENSIONS: INCHES		APVD M. WALMSLEY - 11-29-04	NAME	
		PRODUCT SPEC	KIT, AMP-LATCH DIP PLUG, PREASSEMBLED, .100 X .100 CENTERS,	
		APPLICATION SPEC		
		114-40005		
MATERIAL		WEIGHT	A1 00779 746610	
		CONTACTS: SEE TABLE		
		CUSTOMER DRAWING	SCALE NTS SHEET 1 OF 1 REV H1	