


**Model 109**  
**5 mm Flush Face, Screw Mount LED**




LED lamp mounts flush with panel face. **Mounting Hole Dia.:** 0.197" (5 mm). Nickel plated brass body with Lexan lens. 6" wire leads with 0.250" strip length. Available in the new ultra bright white as well as red, green, yellow, amber, ultra bright blue and ultra bright green.

| Stock No.* | Mfr.'s Type* | Voltage | EACH  |         |         |
|------------|--------------|---------|-------|---------|---------|
|            |              |         | 1-99  | 100-499 | 500-999 |
| 265-109X   | 109-2X       | 2 VDC†  | 9.36  | 8.59    | 7.85    |
| 265-109X   | 109-5X       | 5 VDC   | 9.36  | 8.59    | 7.85    |
| 265-107X   | 109-12X      | 12 VDC  | 9.36  | 8.59    | 7.85    |
| 265-105X   | 109-24X      | 24 VDC  | 9.36  | 8.59    | 7.85    |
| 265-106X   | 109-28X      | 28 VDC  | 9.36  | 8.59    | 7.85    |
| 265-108Y   | 109-5Y       | 5 VDC   | 11.33 | 10.39   | 9.49    |
| 265-107Y   | 109-12Y      | 12 VDC  | 11.33 | 10.39   | 9.49    |
| 265-105Y   | 109-24Y      | 24 VDC  | 11.33 | 10.29   | 9.49    |
| 265-106Y   | 109-28Y      | 28 VDC  | 11.33 | 10.39   | 9.49    |

\*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-ultra bright white where Y appears. †External resistor required.

**Model 500I and 5002 1/2" Snap Mount**



**Model 500I 1/2" Snap Mount Incandescent**

Snap mount incandescent light. **Mounting Hole Dia.:** 0.500" (12.7 mm). High brightness incandescent lamp. Rugged nylon body, Lexan lens. Available in 0.187" O.C. terminals or 6" leads.

**0.187" QC Termination**

| Stock No.* | Mfr.'s Type* | Voltage | EACH |         |         |
|------------|--------------|---------|------|---------|---------|
|            |              |         | 1-99 | 100-499 | 500-999 |
| 265-301X   | 500I-5XQC    | 5 VDC   | 2.26 | 2.03    | 1.87    |
| 265-302X   | 500I-12XQC   | 12 VDC  | 2.26 | 2.03    | 1.87    |
| 265-303X   | 500I-24XQC   | 24 VDC  | 2.26 | 2.03    | 1.87    |
| 265-311X   | 500I-28XQC   | 28 VDC  | 2.26 | 2.03    | 1.87    |

**6" Lead Termination**

|          |           |        |      |      |      |
|----------|-----------|--------|------|------|------|
| 265-304X | 500I-56X  | 5 VDC  | 1.62 | 1.42 | 1.31 |
| 265-305X | 500I-126X | 12 VDC | 1.62 | 1.42 | 1.31 |
| 265-306X | 500I-246X | 24 VDC | 1.62 | 1.42 | 1.31 |
| 265-321X | 500I-286X | 28 VDC | 1.50 | 1.38 | 1.32 |

\*Specify lens color, insert 1-red, 2-green, 3-yellow, 4-amber, 5-blue, 6-clear where X appears.

**Model 5002 1/2" Snap Mount LED**

Snap mount LED light. **Mounting Hole Dia.:** 0.500" (12.7 mm). Rugged nylon body, Lexan lens. Large 10 mm LED. Available in 0.250" O.C. terminals or 6" leads.

**0.250" QC Termination**


|          |            |        |      |      |      |
|----------|------------|--------|------|------|------|
| 265-307X | 5002-5XQC  | 5 VDC  | 1.85 | 1.67 | 1.53 |
| 265-308X | 5002-12XQC | 12 VDC | 1.85 | 1.67 | 1.53 |
| 265-309X | 5002-24XQC | 24 VDC | 1.85 | 1.67 | 1.53 |
| 265-331X | 5002-28XQC | 28 VDC | 1.87 | 1.72 | 1.65 |
| 265-317Y | 5002-5YQC  | 5 VDC  | 3.50 | 3.23 | 3.09 |
| 265-327Y | 5002-12YQC | 12 VDC | 3.50 | 3.23 | 3.09 |
| 265-347Y | 5002-24YQC | 24 VDC | 3.50 | 3.23 | 3.09 |
| 265-332Y | 5002-28YQC | 28 VDC | 3.50 | 3.23 | 3.09 |

**6" Lead Termination**

|          |           |        |      |      |      |
|----------|-----------|--------|------|------|------|
| 265-401X | 5002-56X  | 5 VDC  | 1.78 | 1.57 | 1.44 |
| 265-402X | 5002-126X | 12 VDC | 1.78 | 1.57 | 1.44 |
| 265-403X | 5002-246X | 24 VDC | 1.78 | 1.57 | 1.44 |
| 265-341X | 5002-286X | 28 VDC | 1.78 | 1.57 | 1.44 |
| 265-455Y | 5002-56Y  | 5 VDC  | 2.98 | 2.75 | 2.63 |
| 265-422Y | 5002-126Y | 12 VDC | 2.98 | 2.75 | 2.63 |
| 265-442Y | 5002-246Y | 24 VDC | 2.98 | 2.75 | 2.63 |
| 265-452Y | 5002-286Y | 28 VDC | 2.98 | 2.75 | 2.63 |

\*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

**Model 150**  
**5/32" Snap Mount LED**




Panel mount LED light. **Mounting Hole Dia.:** 0.156" (4.68 mm). Rugged, black nylon body. 6" leads with 0.250" strip length. Available in red, green, yellow, amber, ultra bright blue and pure white.

| Stock No.* | Mfr.'s Type* | Voltage | EACH |         |         |
|------------|--------------|---------|------|---------|---------|
|            |              |         | 1-99 | 100-499 | 500-999 |
| 265-502X   | 150-2X       | 2 VDC†  | 1.18 | 1.03    | .95     |
| 265-503X   | 150-5X       | 5 VDC   | 1.36 | 1.19    | 1.09    |
| 265-504X   | 150-12X      | 12 VDC  | 1.36 | 1.19    | 1.09    |
| 265-501X   | 150-24X      | 24 VDC  | 1.36 | 1.19    | 1.09    |
| 265-505X   | 150-28X      | 28 VDC  | 1.36 | 1.19    | 1.09    |
| 265-506Y   | 150-5Y       | 5 VDC   | 5.28 | 4.74    | 4.36    |
| 265-507Y   | 150-12Y      | 12 VDC  | 5.28 | 4.74    | 4.36    |
| 265-509Y   | 150-24Y      | 24 VDC  | 5.28 | 4.74    | 4.36    |
| 265-508Y   | 150-28Y      | 28 VDC  | 5.28 | 4.74    | 4.36    |

\*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

**T 1 LED Model 205 Panel Mount Fixed Lamp LED**




Incorporates a T-1 size LED in an all metal threaded body. Lamp supplied with flat Lexan transparent lens the same color as the LED and 6" wire leads. **Mounting Hole Dia.:** 0.250" (6.35 mm).

| Stock No.* | Mfr.'s Type* | Voltage | EACH |         |         |
|------------|--------------|---------|------|---------|---------|
|            |              |         | 1-99 | 100-499 | 500-999 |
| 265-270X   | 205-2X       | 2 VDC†  | 6.12 | 5.61    | 5.18    |
| 265-271X   | 205-5X       | 5 VDC   | 6.32 | 5.80    | 5.35    |
| 265-272X   | 205-12X      | 12 VDC  | 6.32 | 5.80    | 5.35    |
| 265-273X   | 205-24X      | 24 VDC  | 6.32 | 5.80    | 5.35    |
| 265-274X   | 205-28X      | 28 VDC  | 6.32 | 5.80    | 5.35    |
| 265-275Y   | 205-5Y       | 5 VDC   | 9.63 | 8.82    | 8.14    |
| 265-276Y   | 205-12Y      | 12 VDC  | 9.63 | 8.82    | 8.14    |
| 265-277Y   | 205-24Y      | 24 VDC  | 9.63 | 8.82    | 8.14    |
| 265-278Y   | 205-28Y      | 28 VDC  | 9.63 | 8.82    | 8.14    |

\*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

**Model 252**  
**5/16" Low Profile Screw Mount LED**




Panel mount LED light. **Mounting Hole Dia.:** 0.156" (4.68 mm) black anodized aluminum body. 6" leads with 0.250" strip length. Available in red, green, yellow, amber, ultra bright green, ultra bright blue and pure white.

| Stock No. | Mfr.'s Type | Voltage | EACH |         |         |
|-----------|-------------|---------|------|---------|---------|
|           |             |         | 1-99 | 100-499 | 500-999 |
| 265-601X  | 252-2X      | 2 VDC†  | 4.57 | 4.09    | 3.76    |
| 265-602X  | 252-5X      | 5 VDC   | 5.13 | 4.60    | 4.23    |
| 265-603X  | 252-12X     | 12 VDC  | 5.13 | 4.60    | 4.23    |
| 265-721X  | 252-24X     | 24 VDC  | 5.13 | 4.60    | 4.23    |
| 265-604X  | 252-28X     | 28 VDC  | 5.13 | 4.60    | 4.23    |
| 265-605Y  | 252-5Y      | 5 VDC   | 8.57 | 7.83    | 7.20    |
| 265-606Y  | 252-12Y     | 12 VDC  | 8.57 | 7.83    | 6.91    |
| 265-731Y  | 252-24Y     | 24 VDC  | 8.57 | 7.83    | 7.20    |
| 265-607Y  | 252-28Y     | 28 VDC  | 8.57 | 7.83    | 7.20    |

\*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

**Panel Mount Indicator Lights**

**Model 240**  
**1/4" Snap Mount LED**




Panel mount LED light. **Mounting Hole Dia.:** 0.250" (6.35 mm). Rugged, black nylon body. 6" leads with 0.250" strip length. Available in red, green, yellow, amber, ultra bright green, ultra bright blue and pure white.

| Stock No.* | Mfr.'s Type* | Voltage | EACH |         |         |
|------------|--------------|---------|------|---------|---------|
|            |              |         | 1-99 | 100-499 | 500-999 |
| 265-404X   | 240-2X       | 2 VDC†  | 1.18 | 1.03    | .95     |
| 265-405X   | 240-5X       | 5 VDC   | 1.36 | 1.19    | 1.09    |
| 265-406X   | 240-12X      | 12 VDC  | 1.36 | 1.19    | 1.09    |
| 265-411X   | 240-24X      | 24 VDC  | 1.36 | 1.19    | 1.09    |
| 265-407X   | 240-28X      | 28 VDC  | 1.36 | 1.19    | 1.09    |
| 265-408Y   | 240-5Y       | 5 VDC   | 5.28 | 4.74    | 4.36    |
| 265-409Y   | 240-12Y      | 12 VDC  | 5.28 | 4.74    | 4.36    |
| 265-411Y   | 240-24Y      | 24 VDC  | 5.28 | 4.74    | 4.36    |
| 265-501Y   | 240-28Y      | 28 VDC  | 5.28 | 4.74    | 4.36    |

\*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

**T -13/4" LED Model 444 Front Flush Mount Indicator Water Resistant**




Low profile design comes with a lens for a neat panel appearance and 6" wire leads. **Mounting Hole Dia.:** 0.312" (7.94 mm). O-ring supplied to seal between the panel and the indicator from dust and water.

| Stock No.* | Mfr.'s Type* | Voltage | EACH  |         |         |
|------------|--------------|---------|-------|---------|---------|
|            |              |         | 1-99  | 100-499 | 500-999 |
| 265-291X   | 444-2X       | 2 VDC†  | 8.63  | 7.97    | 7.62    |
| 265-292X   | 444-5X       | 5 VDC   | 8.68  | 8.02    | 7.66    |
| 265-293X   | 444-12X      | 12 VDC  | 8.68  | 8.02    | 7.66    |
| 265-294X   | 444-24X      | 24 VDC  | 8.68  | 8.02    | 7.66    |
| 265-295X   | 444-28X      | 28 VDC  | 8.68  | 8.02    | 7.66    |
| 265-296Y   | 444-5Y       | 5 VDC   | 11.82 | 10.91   | 10.43   |
| 265-297Y   | 444-12Y      | 12 VDC  | 11.82 | 10.91   | 10.43   |
| 265-298Y   | 444-24Y      | 24 VDC  | 11.82 | 10.91   | 10.43   |
| 265-299Y   | 444-28Y      | 28 VDC  | 11.82 | 10.91   | 10.43   |

\*Specify LED color, insert 1-red, 2-green, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.

**T-1 LED Model 621 Panel Front Mount**



Reflector engineered to allow maximum light distribution. **Mounting Hole Dia.:** 0.236" (6 mm). For panel thickness up to 0.156" (3.97 mm). Metal thread body with 6" wire leads.

| Stock No.* | Mfr.'s Type* | Voltage | EACH |         |         |
|------------|--------------|---------|------|---------|---------|
|            |              |         | 1-99 | 100-499 | 500-999 |
| 265-279X   | 621-2X       | 2 VDC†  | 2.43 | 2.23    | 2.06    |
| 265-280X   | 621-5X       | 5 VDC   | 2.84 | 2.60    | 2.40    |
| 265-281X   | 621-12X      | 12 VDC  | 2.84 | 2.60    | 2.40    |
| 265-283X   | 621-24X      | 24 VDC  | 2.84 | 2.60    | 2.40    |
| 265-284X   | 621-28X      | 28 VDC  | 2.84 | 2.60    | 2.40    |
| 265-285Y   | 621-5Y       | 5 VDC   | 5.15 | 4.75    | 4.54    |
| 265-286Y   | 621-12Y      | 12 VDC  | 5.15 | 4.75    | 4.54    |
| 265-287Y   | 621-24Y      | 24 VDC  | 5.15 | 4.75    | 4.54    |
| 265-288Y   | 621-28Y      | 28 VDC  | 5.15 | 4.75    | 4.54    |

\*Specify LED color, insert 1-red, 2-green, 3-yellow, 4-amber where X appears. Insert 5-ultra bright green, 6-ultra bright blue or 7-pure white where Y appears. †External resistor required.