


284008-3 AS SHOWN



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
POST: COPPER ALLOY, TIN PLATED.

2


SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.




NOT CUMULATIVE TOLERANCE

4

IMO CERTIFICATE WITH SURVEILLANCE IN
CONFORMITY WITH IEC 998-1/998-2-1.


$$\Delta_3 \quad 5.08 \pm 0.05 \quad \longleftrightarrow \quad \longrightarrow \quad \longleftarrow \quad 1.00 \pm 0.02$$

RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

WEIGHT	-
--------	---

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS
OTHERWISE SPECIFIED:

0	PLC
1	PLC
2	PLC
3	PLC

3	PLC
4	PLC
5	PLC

[illegible]

ANGLES
FINISH

WEIGHT	-
--------	---



TE Connectivity

NAME	TERMINAL BLOCK HEADER ASSEMBLY 90 DEGREE WITH EJECTORS 5.08mm PITCH
------	---

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

Λ 200770 © 201008

A300779	G=284008	-
---------	----------	---

SCALE 3.	SHEET	OF	REV B
----------	-------	----	-------