



Omnimate Range - 5.08 mm Pitch



Pin headers SL 5.08/90





Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	12	15	15

*Pollution severity 3 / Overvoltage category III
Additional technical data see page 216

Solder pin length		4.5 mm	4.5 mm		
Color					
Poles	Type	Part No.	Part No.	Qty.	
2	SL 5.08/90/2	1512660000	1512610000	100	
3	SL 5.08/3/90	1512760000	1512710000	100	
4	SL 5.08/4/90	1512860000	1512810000	100	
5	SL 5.08/5/90	1512960000	1512910000	50	
6	SL 5.08/6/90	1513060000	1513010000	50	
7	SL 5.08/7/90	1513160000	1513110000	50	
8	SL 5.08/8/90	1513260000	1513210000	50	
9	SL 5.08/9/90	1513360000	1513310000	50	
10	SL 5.08/10/90	1513460000	1513410000	50	
11	SL 5.08/11/90	1513560000	1513510000	50	
12	SL 5.08/12/90	1513660000	1513610000	50	
13	SL 5.08/13/90	1513760000	1513710000	50	
14	SL 5.08/14/90	1513860000	1513810000	50	
15	SL 5.08/15/90	1513960000	1513910000	50	
16	SL 5.08/16/90	1514060000	1514010000	50	
17	SL 5.08/17/90	1514160000	1514110000	20	
18	SL 5.08/18/90	1514260000	1514210000	20	
19	SL 5.08/19/90	1514360000	1514310000	20	
20	SL 5.08/20/90	1514460000	1514410000	20	
21	SL 5.08/21/90	1514560000	1514510000	20	
22	SL 5.08/22/90	1514660000	1514610000	20	
23	SL 5.08/23/90	1514760000	1514710000	20	
24	SL 5.08/24/90	1514860000	1514810000	20	

Accessories	Page
Mounting	–
Marking	190
Coding	192, 193
Miscellaneous	199

Pin headers SL 5.08/90B





Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	12	15	15

*Pollution severity 3 / Overvoltage category III
Additional technical data see page 216

Solder pin length		4.5 mm	4.5 mm		
Color					
Poles	Type	Part No.	Part No.	Qty.	
2	SL 5.08/2/90B	1514960000	1514910000	100	
3	SL 5.08/3/90B	1515060000	1515010000	100	
4	SL 5.08/4/90B	1515160000	1515110000	100	
5	SL 5.08/5/90B	1515260000	1515210000	50	
6	SL 5.08/6/90B	1515360000	1515310000	50	
7	SL 5.08/7/90B	1515460000	1515410000	50	
8	SL 5.08/8/90B	1515560000	1515510000	50	
9	SL 5.08/9/90B	1515660000	1515610000	50	
10	SL 5.08/10/90B	1515760000	1515710000	50	
11	SL 5.08/11/90B	1515860000	1515810000	50	
12	SL 5.08/12/90B	1515960000	1515910000	50	
13	SL 5.08/13/90B	1516060000	1516010000	50	
14	SL 5.08/14/90B	1516160000	1516110000	50	
15	SL 5.08/15/90B	1516260000	1516210000	50	
16	SL 5.08/16/90B	1516360000	1516310000	50	
17	SL 5.08/17/90B	1516460000	1516410000	20	
18	SL 5.08/18/90B	1516560000	1516510000	20	
19	SL 5.08/19/90B	1516660000	1516610000	20	
20	SL 5.08/20/90B	1516760000	1516710000	20	
21	SL 5.08/21/90B	1516860000	1516810000	20	
22	SL 5.08/22/90B	1516960000	1516910000	20	
23	SL 5.08/23/90B	1517060000	1517010000	20	
24	SL 5.08/24/90B	1517160000	1517110000	20	

Accessories	Page
Mounting	187*
Marking	190
Coding	192, 193
Miscellaneous	199

Pin headers SL 5.08/135



Technical data	VDE	UL	CSA
Rated voltage (V)	250*	300	300
Rated current (A)	12	15	15

*Pollution severity 3 / Overvoltage category III
Additional technical data see page 216

Solder pin length		4.5 mm	4.5 mm		
Color					
Poles	Type	Part No.	Part No.	Qty.	
2	SL 5.08/2/135	1605760000	1635270000	100	
3	SL 5.08/3/135	1605770000	1635280000	100	
4	SL 5.08/4/135	1605780000	1635290000	100	
5	SL 5.08/5/135	1605790000	1635300000	50	
6	SL 5.08/6/135	1605800000	1635310000	50	
7	SL 5.08/7/135	1605810000	1635320000	50	
8	SL 5.08/8/135	1605820000	1635330000	50	
9	SL 5.08/9/135	1605830000	1635340000	50	
10	SL 5.08/10/135	1605840000	1635350000	50	
11	SL 5.08/11/135	1605850000	1635360000	50	
12	SL 5.08/12/135	1605860000			