





NOTE: HARDWARE IS INCLUDED.
SUGGESTED MTG. HOLE .228 DIA.


06



LEAD FINISH: SILVER	
BUSHING FINISH: SILVER	
CAPACITANCE	5500 pF GMV.
TEMP. RANGE	-55°C TO 125°C
CURRENT	10 AMP MAX.
WORKING VOLTAGE	85°C 200 VDC MAX. 125°C 100 VDC MAX.
D.C. RESISTANCE	.01ohms MAX.
MIN. I.L. PER MIL-STD-220 AT 25°C NO LOAD	
FREQ. MHz	I.L. (db)
1	---
10	20
100	68
1 GHz	70
10 GHz	70



MARKING:
PART: SCI 1201-066
BAG: 1201-066
XXX DATE CODE
XXX QTY./BAG
(100/ BAG MAX.)

	6	5	4	3	REV. NO.	TOLERANCES UNLESS OTHERWISE SPECIFIED	api  FAIRVIEW PENNSYLVANIA technologies corp.	
	CN #10201	CN 200667	CN 189629	CN 185003	CHANGE NOTICE	Fractions ± 1/64 Dec. .xx± Dec. .xxx± .010 Angles ±0° 30'		
				REDRAWN		CODE IDENT. NO. DLSP2	Dwn. SLAGLE Ckd. 12-30-14 Apvd. B.DEVINE Scale NONE	Description FILTER, SING, Pi, BSHG 1201-066