



ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

| REVISIONS |     |             | DOC. NO. SPC-F005 * Effective: 12/21/08 * DCP No. B80 |          |        |          |        |          |
|-----------|-----|-------------|-------------------------------------------------------|----------|--------|----------|--------|----------|
| DCP #     | REV | DESCRIPTION | DRAWN                                                 | DATE     | CHECKD | DATE     | APPRVD | DATE     |
| 1950      | A   | RELEASED    | JIN                                                   | 10/22/08 | JWM    | 10/22/08 | JWM    | 10/22/08 |
|           |     |             |                                                       |          |        |          |        |          |



| SPC Type No. | Thread Size | ØA          | B           | C    |
|--------------|-------------|-------------|-------------|------|
| SPC21821     | 2-56        | .171 - .181 | .043 - .050 | 1/4  |
| SPC21822     |             |             |             | 1/2  |
| SPC21823     | 4-40        | .223 - .235 | .061 - .068 | 1/4  |
| SPC21824     |             |             |             | 1/2  |
| SPC21825     |             |             |             | 3/4  |
| SPC21826     | 6-32        | .275 - .290 | .078 - .087 | 3/16 |
| SPC21827     |             |             |             | 1/4  |
| SPC21828     |             |             |             | 3/8  |
| SPC21829     |             |             |             | 1/2  |
| SPC21830     | 8-32        | .326 - .344 | .095 - .105 | 3/4  |
| SPC21831     |             |             |             | 1/4  |
| SPC21832     |             |             |             | 3/8  |
| SPC21833     |             |             |             | 1/2  |
| SPC21834     | 10-32       | .378 - .399 | .112 - .123 | 3/4  |
| SPC21835     |             |             |             | 1/2  |
| SPC21836     |             |             |             | 3/4  |



Material: Steel, Nickel Plated

DISCLAIMER:  
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

|              |  |          |                                 |          |                 |               |
|--------------|--|----------|---------------------------------|----------|-----------------|---------------|
| DRAWN BY:    |  | DATE:    | DRAWING TITLE:                  |          |                 |               |
| Jason Nash   |  | 10/22/08 | BINDER HEAD STEEL MACHINE SCREW |          |                 |               |
| CHECKED BY:  |  | DATE:    | SIZE                            | DWG. NO. | ELECTRONIC FILE | REV           |
| JWM          |  | 10/22/08 | A                               | TA-966   | TA-966.DWG      | A             |
| APPROVED BY: |  | DATE:    | SCALE:                          | NTS      | U.O.M.: INCHES  | SHEET: 1 OF 1 |
| JWM          |  | 10/22/08 |                                 |          |                 |               |

