


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PART NUMBER	MATERIAL	MARKER SIZE inches [mm]	COLOR (PMS)	LABELS SHEET	SHEET QTY.	STD. PKG. QTY.
S100X225YAJ	GMY6 CLEAR POLYESTER FILM	1.000 [25.4] X 2.250 [57.2]	WHITE	32	32	1000
S100X225YBJ			BLUE (291C)			
S100X225YCJ			BROWN (465C)			
S100X225YDJ			GREEN (353C)			
S100X225YEJ			GRAY (422C)			
S100X225YFJ			ORANGE (150C)			
S100X225YGJ			PURPLE (264C)			
S100X225YHJ			RED (184C)			
S100X225YIJ			YELLOW (101C)			
S100X225YAJ-D			WHITE	16	16	500
S100X225YBJ-D			BLUE (291C)			
S100X225YDJ-D			GREEN (353C)			
S100X225YHJ-D			RED (184C)			
S100X225YIJ-D			YELLOW (101C)			

CAD FILENAME/LAYERS		100472CF_DC_C10206/00A	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
CUSTOMER DRAWING OPTIMUMM SELF-LAM.		LASER INKJET PRINTABLE LABELS	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (.XXX) ± .025 (.XX) ± .050 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY RVU		MAT'L:	
DATE 9/22/04		SEE TABLE	
CHK'D		SCALE NTS	
REV		DRAWING NO. C10206	
DATE		DWG A SIZE	
BY			
CHK			

2	8-12-08	RVU	CHG. FORMAT FROM 'B' TO 'A' SIZE. TITLE AREA TOL. INCORRECT.	5516	R				
1	9-12-06	RVU	ADDED PART NUMBER WITH -D.	4680	R				
0	6-29-06	RVU	DRAWING RELEASE. MAT'L WAS GMY2.	4568	R				
A	9-22-04	RVU	ENGRG. RELEASE.	0000	R				
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	