

Search Results

Evaluate

- FAQ's

Design a Solution

- Catalog Cut Sheet
- PDF-CN1 Product
- Part Drawings
- DWG-NET-ACCESS C ..
- DXF-NET-ACCESS C ..
- PDF-NET-ACCESS C ..
- Specification Sheets
- PDF-Net-Access S ..

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Install & Maintain

- Installation Instructions
- PDF-Net-Access C ..

Home > Product On-Line Catalog > Search Results >

Current refinements (click ☐ to remove) Search Tips 

☒ Text Search: 'CN3CN'

Your search criteria matched only one product, shown below

CN3CN



Net-Access™ Switch Cabinets

- Inset frame posts creating large and accessible vertical pathways for routing cables
- Modular cable management fingers easily mount to the front and/or back of all four cabinet posts
- Designed with the use of CFD (Computational Fluid Dynamics) analysis and thermal lab testing to optimize the thermal performance of network switches requiring side-to-side airflow
- Innovative, fully integrated, electrically bonded cabinet with a single ground connection to guard against ESD, and provide a safe current path to ground
- Accommodates equipment mounting depths up to 25.9" (658mm)
- Four adjustable equipment mounting rails – available in cage nut or #12-24 threaded with printed rack space identification
- Doors include keyed swing handles
- Side panels include keyed pushbutton latches
- Durable black polyester epoxy powder coat finish

- 2500 lbs. (1134 kg) load rating
 - Cabinet ships assembled, one per pallet
 - For the complete grounding solution, see the StructuredGround™ Kits for Cabinets.
 - Designed specifically for use with Net-Access™ Switch and Server Cabinets
- Cage Nut available for CN1, CN2 and CN3 only, specify CN*CN, i.e. CN1CN.

▪ Part Number	CN3CN
▪ RoHS Compliancy Status	Compliant
▪ Part Description	Cabinet frame with top panel. Two sets of #12-24 cage nut equipment mounting rails. 45 RU cable management on front and rear of front posts. Dimensions: 84.0"H x 31.5"W x 40.0"D (2134.0mm x 800.0mm x 1016.0mm)
▪ Material	Steel
▪ Color	Black
▪ Depth (In.)	41.1
▪ Depth (mm)	1016
▪ Height (In.)	84
▪ Height (mm)	2134
▪ Width (In.)	31.5
▪ Width (mm)	800
▪ No. of Rack Spaces	45
▪ Pricing Description	Network Cabinet Frame Only, 45 RU, Cage Nut Rails
▪ Min. Order UOM	PC
▪ Min. Order Qty.	1
▪ BOM Qty. (# of Pkgs.)	<input type="text" value="0"/>
▪ Add to Favorite Product List	<input type="button" value=""/>

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.