





Loading-Plan (Data)	
Shield	
1	White/green
2	Green
3	White/orange
4	Blue
5	White/blue
6	Orange
7	White/brown
8	Brown


Loading-Plan (Power)	
L1	black
N	blue
PE	green/yellow

-Protection level: IP67
-Temperature range: -20°C ...+70°C

-Data transmission properties in accordance
with ISO/IEC 11801:2002? ? Class? D ? R??

4	Hybrid cable 4x2AWG26/7+3x2.5 mm² AC	33 57 111 020 0002	20 m
3	Hybrid cable 4x2AWG26/7+3x2.5 mm² AC	33 57 111 010 0002	10 m
2	Hybrid cable 4x2AWG26/7+3x2.5 mm² AC	33 57 111 005 0002	5 m
1	Hybrid cable 4x2AWG26/7+3x2.5 mm² AC	33 57 111 001 0002	1 m

Cont No.	Type of cable	Part-No.	Dim. a
----------	---------------	----------	--------



 All Dimensions in mm Original Size DIN A 3			Techn. Character.				Nicht tolerierte Maß/Free size tolerances				
				Dat.	Name	Maßstab/Scale 2:1	Hybrid cable assembly, 4x2AWG26/7+3x2.5 mm ² HAN3A, AC				
			Detail.	07.07.08	RA						
			Insp.								
			Stand.								
35035	10.11.08	MS	HARTING Electronics GmbH & Co. KG					TB 33 57 111 xxx 0002			
34567			D-32339 ESPELKAMP								
Mod.	Dat.	Name					Sub.	Blatt/ page /			