







[illegible]



RECOMMENDED PCB LAYOUT
RECOMMENDED PCB THICKNESS: 1.6mm
TOLERANCE: $\pm 0.05\text{mm}$ (TOP VIEW)



DETAIL Z
SCALE 2:1

DETAIL Y
SCALE 2:1

mat'l. code				surface ASME Y14.5	tolerance ASME Y14.5	projection	product family			
ltr	ecn no	dr	date	tolerances unless otherwise specified			GANGED MJACK			
A				angles	X.X $\pm$ 0.25		title CAT 3 MULTIPORT STACKED 2x2 WITH SHIELD, W/O LED			
				mm	X.XX $\pm$ 0.13					
				X $\pm$ 1"	X.XXX $\pm$ 0.05					
				dr	WENDY CHEN 05/03/11		dwg no		sheet 2 of 3	size
				enr	WENDY CHEN 05/03/11		10118070			A4
				chr	WENDY CHEN 05/03/11		type		CUSTOMER Drawing	
				appd	GARY HSIEH 05/03/11					
sheet index	revision	sheet								

NOTE:

1. MATERIAL:

HOUSING & INNER HOUSING & COVER:
HIGH TEMPERATURE THERMOSPLASTIC, UL94V-0, COLOR: BLACK.
CONTACTS: COPPER ALLOY.
SHIELD: COPPER ALLOY.
INNER SHIELD: COPPER ALLOY.

2. FINISH:

CONTACTS: 50u" MIN. NICKEL UNDER PLATED OVER ALL.
SELECTIVE GOLD PLATED ON CONTACT AREA,
1u" GOLD PLATED ON SOLDER TAIL.

SHIELD & INNER SHIELD: 20u" MIN. NICKEL OVER ALL.

3. LASER MARK FCI LOGO ON THE TOP OF SHIELD.

4. "DATE CODE" DESCRIPTION:

XX XX
WEEK
YEAR (EX. : 10--2010)


5. PRODUCT PERFORMANCE PER SPEC. : GS-12-0990.

6. PACKING SPEC. : GS-14-2170.


7. THIS PRODUCT MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBED
IN GS-22-008.8. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 5 SECONDS IN A WAVE SOLDER APPLICATION WITH A CIRCUIT BOARD.

9. PART NUMBER DESCRIPTION:

10118070-X X X X X X X LF
LEAD FREE
0 : RESERVED (NOT USED)
PACKAGING
1 : TRAY
OPTIONAL BACK SHIELD TAB
1 : WITH 1 BACK SHIELD TAB
OPTIONAL RIGHT / LEFT SHIELD TAB
A : SHIELD TAB WITH INNER SHIELD
B : SHIELD TAB WITHOUT INNER SHIELD
OPTIONAL PANEL GROUND
0 : WITHOUT PANEL GROUND
LED COLOR
0 : WITHOUT LED
CONTACT AREA PLATING
1 : 15u" GOLD PLATING
2 : 30u" GOLD PLATING
5 : 1u" GOLD FLASH PLATING



10118070-XXXAXXXLF
(WITH INNER SHIELD)



10118070-XXXBXXXLF
(WITHOUT INNER SHIELD)

mat'l. code				surface ASME Y14.5 ✓		tolerance ASME Y14.5		projection 		product family GANGED MJACK									
ltr	ecn no		dr	date		tolerances unless otherwise specified						title CAT 3 MULTIPORT STACKED 2x2 WITH SHIELD, W/O LED							
A						angles		linear		X.X±0.25								MM [INCH]	
										X.XX±0.13									
						X°±1°				X.XXX±0.05		scale							
						dr	WENDY CHEN		05/03/11				dwg no		sheet 3 of 3		size		
						enr	WENDY CHEN		05/03/11				10118070				A4		
						chr	WENDY CHEN		05/03/11										
						appd	GARY HSIEH		05/03/11										
sheet index		revision sheet																	