


PANDUIT PART NO.	PK	HOUSING COLOR	WIRE RANGE	MAX INSUL DIAMETER
DV18-250P	-LY -MY	RED	#22-18	.13 (3.3)
DV14-250P	-L -M	BLUE	#16-14	.16 (4.1)


NOTES:

- 300 V. MAX. VOLTAGE RATING
- 194° F (90° C) MAX. TEMP. RATING
- FOR STRANDED COPPER WIRE ONLY -
WIRE STRIP LENGTH $1/4"^{+1/32}_{-0}$ (6.3 $^{+0.8}_{-0}$)
- PACKAGE QTY: STD. PKG. -L, -LY=100
BULK PKG. -M, -MY=1000
- RECOMMENDED INSTALLATION TOOLS: CT-100, CT-160,
CT-250, CT-500, CT-550
- DIMENSIONS IN BRACKETS ARE IN MILLIMETERS

.250 X .032
(6.3 X .8)
TAB SIZE



COLOR CODED
VINYL HOUSING



08	9/09	BCT	BCT	REINSTATED DV18-250P-MY				PANDUIT CORP. TINLEY PARK, ILLINOIS .250 VINYL INSUL. PIGGYBACK DISCONNECT FOR #22-18 AND #16-14 AWG WIRE SIZES
07	8/09	BCT	BCT	REMOVED DV18-250P-MY				
06	8/09	BCT	BCT	MODIFIED PKG CODES TO -LY AND -L				
05	7/06	DAW	DAW	ADDED -CY, -MY PACKAGE QTY. FOR DV18-250P	TR00145			
REV	DATE	BY	CHK	DESCRIPTION	ECN #	CUST	PM	DRAWN BY DAW CHK'D SCALE NONE DRAWING NO. A41208