

Quick open spanner

A quick action ratchet-type tube wrench for tube fitting applications such as hydraulic, pneumatic, refrigeration or other fasteners using hex. Jaws open up to clamp over inline fittings.


Finish: Black phosphated

Material: Chrome-Vanadium

Ratcheting tube wrench

1322Z

				A mm	B mm	C mm	
1322Z-3/8	7314150132874	1	3/8	138	26	7	72
1322Z-7/16	7314150132881	1	7/16	138	26	7	72
1322Z-1/2	7314150132898	1	1/2	138	26	7	72
1322Z-9/16	7314150132904	1	9/16	184	34	10	142
1322Z-5/8	7314150132911	1	5/8	184	34	10	142
1322Z-11/16	7314150132928	1	11/16	184	34	10	142
1322Z-3/4	7314150132935	1	3/4	184	34	10	142
1322Z-13/16	7314150132942	1	13/16	238	43	11	263
1322Z-7/8	7314150132959	1	7/8	238	43	11	263
1322Z-15/16	7314150132966	1	15/16	238	43	11	263
1322Z-1	7314150132973	1	1	238	43	11	263



Drive: 1 1/2

Finish: forged, phosphated

Material: CHROMO-EXTRA

Torque according to DIN and ASME

T=depth of female shank

With Dynamic-Drive-Profile

Manufactured on demand

				L mm	D1 mm	D2 mm	T mm		
K9806M-41	7314150130986	1	41	114.3	71.0	82.6	27.4	K560F-8	2640
K9806M-46	7314150130993	1	46	120.7	76.8	82.6	30.6	K560F-8	3110
K9806M-50	7314150131006	1	50	127.0	81.5	82.6	33.1	K560F-8	3480
K9806M-55	7314150131013	1	55	127.0	87.5	82.6	36.3	K560F-8	3950
K9806M-60	7314150131020	1	60	133.4	93.3	82.6	39.5	K560F-8	4420
K9806M-65	7314150131037	1	65	139.7	99.3	82.6	42.7	K560F-8	4890
K9806M-70	7314150131044	1	70	146.1	105.2	82.6	45.9	K560F-8	5350
K9806M-75	7314150131051	1	75	152.4	111.1	82.6	49.1	K560F-8	5580
K9806M-80	7314150131068	1	80	158.8	117.0	82.6	52.3	K560F-8	7240
K9806M-85	7314150131075	1	85	165.1	122.8	82.6	55.5	K560F-8	7830
K9806M-90	7314150131082	1	90	171.5	128.8	82.6	58.7	K560F-8	9070
K9806M-95	7314150131099	1	95	177.8	134.6	82.6	61.9	K560F-8	9980
K9806M-100	7314150131105	1	100	184.2	140.6	82.6	65.1	K560F-8	10910
K9806M-105	7314150131112	1	105	190.5	146.4	82.6	68.3	K560F-8	11820
K9806M-110	7314150131129	1	110	196.9	152.4	82.6	71.5	K560F-8	12740
K9806M-115	7314150131136	1	115	203.2	158.2	82.6	74.7	K560F-8	13650
K9806M-120	7314150131143	1	120	209.6	164.2	82.6	77.9	K560F-8	14580

Sockets Metric, long

K9806M

