



# D38999/43 Jam Nut Mount Hermetic Receptacle MIL-DTL-38999 Series IV

## How To Order: MS

**Basic Specification**  
*D38999*

**Connector Material / Finish**  
*N* - CRES, Nickel  
*Y* - CRES, Passivated

**Insert Arrangement**  
Per MIL-STD-1560;  
See Pages B2 - B4

**Alternate Key Position**  
*A, B, C, D, K, L, M, R, U*  
(*N* = Normal)

D38999

/43

Y

B

35




P

N

**Shell Style**  
*/43* - Jam Nut Mount

**Shell Size**  
*B* - 11   *F* - 19  
*C* - 13   *G* - 21  
*D* - 15   *H* - 23  
*E* - 17   *J* - 25

**Contact Termination**  
*P* - Pin, Solder Cup   *S* - Socket, Solder Cup  
*X* - Pin, Eyelet   *Z* - Socket, Eyelet  
*C* - Pin, PCB   *D* - Socket, PCB  
Flex Feedthrough   Flex Feedthrough



Dimensions in Inches (millimeters) are subject to change without notice.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## Glenair:

[D38999/43NB35PA](#) [D38999/43NB35PB](#) [D38999/43NB35PC](#) [D38999/43NB35PN](#) [D38999/43NB5PN](#)  
[D38999/43NC35PN](#) [D38999/43NC4PN](#) [D38999/43NC98PN](#) [D38999/43ND18PN](#) [D38999/43ND35CN](#)  
[D38999/43ND35PB](#) [D38999/43ND35PN](#) [D38999/43NE26PN](#) [D38999/43NE35PN](#) [D38999/43NE6PN](#)  
[D38999/43NE8PN](#) [D38999/43NF11PN](#) [D38999/43NF32PN](#) [D38999/43NF35PN](#) [D38999/43NG11PN](#)  
[D38999/43NG35PA](#) [D38999/43NG35PB](#) [D38999/43NG35PN](#) [D38999/43NG41PN](#) [D38999/43NH35PN](#)  
[D38999/43NH55PN](#) [D38999/43NJ29PN](#) [D38999/43NJ35PN](#) [D38999/43NJ61PD](#) [D38999/43NJ61PN](#)  
[D38999/43YB35PN](#) [D38999/43YB5CN](#) [D38999/43YB5PN](#) [D38999/43YB98PN](#) [D38999/43YB99PN](#)  
[D38999/43YC35PN](#) [D38999/43YC4PN](#) [D38999/43YC98PN](#) [D38999/43YD18PN](#) [D38999/43YD35PN](#)  
[D38999/43YD5PN](#) [D38999/43YE26PN](#) [D38999/43YE35PN](#) [D38999/43YF11PN](#) [D38999/43YG11PB](#)  
[D38999/43YG41PN](#) [D38999/43YJ61PN](#) [D38999/43NB35DA](#) [D38999/43NB35DB](#) [D38999/43NB35DC](#)  
[D38999/43NB35DD](#) [D38999/43NB35DK](#) [D38999/43NB35DN](#) [D38999/43NB35SA](#) [D38999/43NB35SB](#)  
[D38999/43NB35SC](#) [D38999/43NB35SD](#) [D38999/43NB35SK](#) [D38999/43NB35SN](#) [D38999/43NB35ZA](#)  
[D38999/43NB35ZB](#) [D38999/43NB35ZC](#) [D38999/43NB35ZD](#) [D38999/43NB35ZK](#) [D38999/43NB35ZN](#)  
[D38999/43NB4DA](#) [D38999/43NB4DB](#) [D38999/43NB4DC](#) [D38999/43NB4DD](#) [D38999/43NB4DK](#) [D38999/43NB4DN](#)  
[D38999/43NB4SA](#) [D38999/43NB4SB](#) [D38999/43NB4SC](#) [D38999/43NB4SD](#) [D38999/43NB4SK](#) [D38999/43NB4SN](#)  
[D38999/43NB4ZA](#) [D38999/43NB4ZB](#) [D38999/43NB4ZC](#) [D38999/43NB4ZD](#) [D38999/43NB4ZK](#) [D38999/43NB4ZN](#)  
[D38999/43NB5DA](#) [D38999/43NB5DB](#) [D38999/43NB5DC](#) [D38999/43NB5DD](#) [D38999/43NB5DK](#) [D38999/43NB5DN](#)  
[D38999/43NB5SA](#) [D38999/43NB5SB](#) [D38999/43NB5SC](#) [D38999/43NB5SD](#) [D38999/43NB5SK](#) [D38999/43NB5SN](#)  
[D38999/43NB5ZA](#) [D38999/43NB5ZB](#) [D38999/43NB5ZC](#) [D38999/43NB5ZD](#) [D38999/43NB5ZK](#)