



English | 简体中文 | 日本語

Search Entire Site [GO](#)

[Contact IDT](#) | [Investors](#) | [Press](#)

[About IDT](#)

[Products](#)

[Applications](#)

[Support](#)

[myIDT](#)

[Document Search](#) | [Package Search](#) | [Parametric Search](#) | [Cross Reference Search](#) | [Green & RoHS](#) | [Calculators](#) | [Thermal Data](#) | [Reliability & Quality](#) | [Military](#)

[Home](#) > [Products](#) > > [841204A](#) > [841204AK-245LFT](#)

[Add to myIDT \[?\]](#)

You may also like...

841204AK-245LFT

Category:

Generic Part:

Market Group:

Description:

[841204A](#)

NETCOM

4 HCSL OUT SYNTHESIZER

**Time is
money**

Parameters

Package	VFQFP 32 (NLG32)
Speed	NA
Temperature	C
Voltage	3.3 V
Status	Active
Sample	No
Minimum Order Quantity	2500
Factory Order Increment	2500

Distributor Inventory

No Pricing information is available from our Distributors at this time.

Documents

No documents available for this part at this time.

Package

Description	VFQFN-N 5 X 5 X 1.0MM NO LEAD
Class	PLASTIC
Moisture Sensitivity Level (MSL)	3
Category	Green
Moisture Exposure Floor Life	168 hrs. @ <30°C/60%RH
Peak Reflow Temperature	260°C
Rebake Conditions	48 hrs.@125°C
Length	5.0
Mark	NLG
Width	5.0
Pitch	0.5
Thickness	1.0
Status	Active

[Home](#) | [Site Map](#) | [Legal](#) | [Careers](#) | [Contact Us](#) | [Quality](#) | [RSS](#) What is this?

Use of this website signifies your agreement to the [acceptable use](#) and [privacy policy](#). Copyright © 1997-2008 Integrated Device Technology, Inc. [All Rights Reserved](#).