

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1301080156](#)
Status: **Active**
Overview: [Wide-Area Lighting Products](#)
Description: Super-Safeway Twin Tube 30W Fluorescent Work Light with 16/3 SJOW Feed Thru 7.62m (25.0') Cord Length



Documents:
[Brochure \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E174254

General

Product Family Portable Lighting
Series [130108](#)
NEMA Configuration NEMA 5-15
Outlet Feed-Through
Overview [Wide-Area Lighting Products](#)
Product Name Super-Safeway
Type Wide Area Lamps
UPC 78678867262

Physical

Cord Length - Primary 7.62m (25.0')
Cord Length - Secondary 0.152m (6.00")
Depth 190.75mm (7.510")
Duty Industrial
Guard Included No
Guard Type N/A
Height 82.55mm (3.250")
Length 625.35mm (24.620")
Material - Globe Butyrate
Material - Guard Nitrile Rubber 80 Shore A
Mounting Style Adjustable Brackets
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Fluorescent
Cord Type - Primary 16/3 SJOW
Lamp Type F15/T8
Lamp Wattage - Maximum 30W
Lumens 1820
On/Off Switch No
Voltage (Fixture) - Maximum 120VAC 60 HZ

Material Info

Engineering Number 1334

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[130108](#) Series