




## Wiha Dynamic Series Screwdrivers - Slotted & Phillips



| 510 90 Set 5 Pc. Slotted & Phillips, Wiha-Dynamic Handle |         |          |         |          |         |          |         |          |      |
|----------------------------------------------------------|---------|----------|---------|----------|---------|----------|---------|----------|------|
| Item No.                                                 | Slotted | Phillips | Slotted | Phillips | Slotted | Phillips | Slotted | Phillips |      |
|                                                          | mm      | Inch     | mm      | Inch     | Size    | mm       | Inch    | lbs.     | pkg. |
| 510 90                                                   | 3.0     | .118     | 80      | 3.1      | 0       | 60       | 2.3     | .68      | 1    |
|                                                          | 4.0     | .157     | 100     | 3.9      | 1       | 80       | 3.1     |          |      |
|                                                          | 5.5     | .216     | 125     | 4.9      |         |          |         |          |      |

| 510 92 Set 4 Pc. Slotted, Wiha-Dynamic Handle |         |         |         |         |         |         |         |      |      |
|-----------------------------------------------|---------|---------|---------|---------|---------|---------|---------|------|------|
| Item No.                                      | Slotted | Slotted | Slotted | Slotted | Slotted | Slotted | Slotted | lbs. | pkg. |
|                                               | mm      | mm      | Inch    | mm      | mm      | Inch    |         |      |      |
| 510 92                                        | 2.0     | 65      | 2.5     | 5.5     | 125     | 5.0     |         | 1    | .58  |
|                                               | 3.0     | 80      | 3.1     | 6.5     | 150     | 6.0     |         |      |      |



**510 Slotted Screwdriver, With Wiha-Dynamic Handle**  
Blade high alloy chrome-vanadium-molybdenum steel, hardened, hard chromed. Wiha-Dynamic-handle high quality plastic.

| Item No. | Slotted | Slotted | Slotted | Slotted | Slotted | Slotted | Slotted | Slotted | lbs. | pkg. |
|----------|---------|---------|---------|---------|---------|---------|---------|---------|------|------|
|          | mm      | Inch    | mm      | Inch    | mm      | Inch    | mm      | Inch    |      |      |
| 510 20   | 2.0     | .08     | 65      | 2.5     | 0.4     | .02     | 165     | 6.5     | .04  | 10   |
| 510 25   | 2.5     | .10     | 75      | 3.0     | 0.4     | .02     | 175     | 6.9     | .04  | 10   |
| 510 30   | 3.0     | .12     | 80      | 3.1     | 0.5     | .02     | 180     | 7.1     | .05  | 10   |
| 510 35   | 3.5     | .14     | 100     | 3.9     | 0.6     | .02     | 205     | 8.1     | .07  | 10   |
| 510 40   | 4.0     | .16     | 100     | 3.9     | 0.8     | .03     | 205     | 8.1     | .08  | 10   |
| 510 55   | 5.5     | .22     | 125     | 5.0     | 1.0     | .04     | 236     | 9.3     | .14  | 10   |
| 510 65   | 6.5     | .26     | 150     | 5.9     | 1.2     | .05     | 267     | 10.5    | .20  | 10   |
| 510 80   | 8.0     | .32     | 175     | 7.0     | 1.2     | .05     | 267     | 11.6    | .29  | 10   |



| 510 99 Set 11 Pc. Slotted & Phillips, Wiha-Dynamic Handle |         |         |         |         |         |         |         |      |      |
|-----------------------------------------------------------|---------|---------|---------|---------|---------|---------|---------|------|------|
| Item No.                                                  | Slotted | Slotted | Slotted | Slotted | Slotted | Slotted | Slotted | lbs. | pkg. |
|                                                           | mm      | Inch    | mm      | Inch    | Size    | mm      | Inch    |      |      |
| 510 99                                                    | 2.0     | .078    | 65      | 2.5     | 0       | 60      | 2.3     | 1.3  | 1    |
|                                                           | 2.5     | .098    | 75      | 3.0     | 1       | 80      | 3.1     |      |      |
|                                                           | 3.0     | .118    | 80      | 3.1     | 2       | 100     | 4.0     |      |      |
|                                                           | 3.5     | .139    | 100     | 3.9     |         |         |         |      |      |
|                                                           | 4.0     | .157    | 100     | 3.9     |         |         |         |      |      |
|                                                           | 5.5     | .216    | 125     | 5.0     |         |         |         |      |      |
|                                                           | 6.5     | .255    | 150     | 5.9     |         |         |         |      |      |
|                                                           | 8.0     | .315    | 175     | 7.0     |         |         |         |      |      |



| 511 Phillips Screwdriver, With Wiha-Dynamic Handle |      |     |      |     |      |     |      |      |      |
|----------------------------------------------------|------|-----|------|-----|------|-----|------|------|------|
| Item No.                                           | Size | mm  | Inch | mm  | Inch | mm  | Inch | lbs. | pkg. |
| 511 05                                             | 0    | 60  | 2.4  | 3.0 | 1/8  | 160 | 6.3  | .05  | 10   |
| 511 10                                             | 1    | 80  | 3.1  | 4.5 | 3/16 | 191 | 7.5  | .11  | 10   |
| 511 20                                             | 2    | 100 | 3.9  | 6.0 | 1/4  | 217 | 8.5  | .17  | 10   |