

You are here: [Products](#) » [Connectors f.con](#) » [PCB connectors](#) » [Male headers](#) » [SL 3 ... / SLK 3 ...](#) » [SL 3 025](#)

Male headers

SL 3 025 36 Z

male header square 0.635 mm, "dimensions A + B" changeable

add to request



Features Technical Drawing Variants Accessories / related products

no. of contacts	36
contact material	CuSn-Legierung
surface contact / contact sleeve	Ni+0,2µm Au Ni+4...6µm Sn
surface of contact	tin-plated
volume resistivity	≤5 mΩ
nominal current	3 A
nominal voltage	250 V AC
test voltage	2000 V
material isolation body	PA 4.6, GF
temperature range	-40 °C ... +163 °C (260 °C / 10 s)
class of flammability	UL 94 V-0
insulation resistance	>10 ¹² Ω
connection type	soldering
version	insertion side "dimension C" changeable, "S" selective gold-plated
reflow solderable	yes