

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

ALL RIGHTS RESERVED.

© COPYRIGHT — By —

LOC

	DIST
--	------

REVISIONS

A

50

	F
--	---

LT

DESCRIPTION

DATE _____

DW

	APVD
--	------

1


REVISÉD PER ECR-13-004343

30JUL13


KH

KR

- 1 MATES WITH $.020 \pm .001 \times .187$ TAB
- 2 WIRE STRIP LENGTH .281
- 3 INSULATION SIZE .160 MAX DIA
- 4 CONTINUOUS STRIP ON REELS
- 5 DIMENSION DOES NOT INCLUDE TRIM BURR
- 6 .015 MAX CARRIER TRIM BURR PER SIDE IS ALLOWABLE IN THE SHADED AREA.



BULK		HOUSING: NYLON, COLOR—BLUE TRANSLUCENT RECEPTACLE: BRASS		5—350815—2	
STANDARD		TIN		3—350815—2	
PACKAGING		MATERIAL & FINISH		PART NO	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P FORTNEY 11/7/88		 TE Connectivity	
		CHK MS FEHER 11/7/88			
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME	
		APVD K RANDOLH 11/7/88 PRODUCT SPEC 108—2043 APPLICATION SPEC 114—2123		RECEPTACLE ASSY, ULTRA—FAST, .187 SERIES, 16—14 AWG	
MATERIAL SEE TABLE		FINISH SEE TABLE		SIZE A3	CAGE CODE 00779
		WEIGHT —		DRAWING NO C—350815	RESTRICTED 1 —
CUSTOMER DRAWING				SCALE 4:1	SHEET 1 OF 1
				REV S	