

ALPHASTAT 16

Ausführung MONO mit Tragkäfig/single turn with bracket

Typ 63250-214XX


Welle/shaft 4 mm L=30 mm

Buchse/bushing M7x0,75





Printausführung/for printed circuit

Drehbereich/Rotation angle 270° +5%

Belastbarkeit/rated wattage lin 0,2W/log 0,05 W



63250-214XX



	Standard 63250-21400/—			Mittenrast/center click 63250-21410/—			Rast 11/11 clicks 63250-21420/—			Rast 41/41 clicks 63250-21440/—		
	lin	poslog	neglog	lin	poslog	neglog	lin	poslog	neglog	lin	poslog	neglog
1 k	449883											
2,5 k												
5 k												
10 k	449896											
25 k												
50 k												
100 k	449909											
250 k												
500 k												
1 M												

lagermässige Ausführungen