

	YORKEX H/HARD (T/X)			YORKEX HARD				YORKEX CHROME PLATED			
O/D Wall MM	Stock Lth		Press 65C	O/D Wall MM	Stock Lth		Press 65C	O/D Wall MM	Stock Lth		Press 65C
	3mtr	6mtr	Bar		3mtr	6mtr	Bar		3mtr	6mtr	Bar
12x0.6	✓	*	63	35x1.0	✓	✓	42	15x0.7	✓	✓	58
15x0.7	✓	✓	58	42x1.0	✓	✓	35	22x0.9	✓	✓	51
22x0.9	✓	✓	51	54x1.0	✓	✓	27	28x0.9	✓		40
28x0.9	✓	✓	40	67x1.2	✓	✓	26	35x1.2	✓		51
35x1.2	✓	✓	42	76x1.5	✓	✓	29	42x1.2	✓		42
42x1.2	✓	✓	35	108x1.5	✓	✓	20	54x1.2	✓		33
54x1.2	✓	✓	27								

O/D Wall MM	KUTERLON (T/Y)			KUTERLON PLASTIC COATED				MINIBORE ANNEALED			
	3mtr		Press 65C Bar	O/D Wall MM	6mtr	25mtr	Press 65C Bar	O/D Wall MM	10mtr	25mtr	Press 65C Bar
	LTHS				LTHS	Coil			Coil	Coil	
12x0.8	✓		67	8x0.6		✓	66	6x0.6		✓	90
15x1.0	✓		87	10x0.7		✓	62	8x0.6	✓	✓	66
22x1.2	✓		69	15x0.7	✓	✓	58	10x0.6	✓	✓	62
28x1.2	✓		56	15x1.0		✓	67				
35x1.5	✓		65	22x1.2	✓	✓	57				
42x1.5	✓		54								
54x2.0	✓		56								

Yorkshire copper tube 6-159mm, can be trusted to convey fluids/gases ranging from -196c+205c
 Yorkshire copper carries a 25 year guarantee against product failure directly attributable to a
 manufacturing defect. Please contact our sales office for the suitability of each product range. This
 is a sample range that Yorkshire copper offer, see their full catalogue for further details.



CHOICE AND QUALITY FROM YORKSHIRE

- Yorkex and Kuterlon general purpose plain tube • Minibore coils
- Kuterlex and Kuterlex pre-coated tubes for external protection
- WICU Gas yellow pre-coated coils for gas services
- Yorkshire Medical degreased tube (to BS EN 13348) • Yorkex Chrome-plated tube

All BSI Kitemark certified and backed by Yorkshire's 25 year guarantee.

Choose Yorkshire Copper Tube: ask for it by name.



Ask for it by name

Copper Pressfittings 12mm – 108mm (Stock range shown)
WRAS/KIWA Approved. Suitable for Hot/Cold & Heating Services

SAN1 6270 Straight Coupling 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		SAN6 6243 Reducer Insert 22x15mm 42x22mm 28x15mm 28x22mm 35x22mm 35x28mm		SAN12s 6001A 90 Street Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	
SAN2 8270G Female Adaptor 15mmx½ 22mmx¾ 28mmx1 35mmx1¼ 42mmx1½		SAN6 6243 Reducer Insert 42x 28mm 42x35mm 54x35mm 54x42mm 67x28mm		SAN21 6041 45 Elbow F/F 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	
SAN2 8270G Female Adaptor 54mmx2 67mmx2½		SAN6 6243 Reducer Insert 67x35mm 67x42mm 67x54mm 76x42mm 76x54mm		SAN21s 6040 45 Str Elbow M/F 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	
SAN3 8243G Male Adaptor 15mmx½ 22mmx¾ 28mmx1 35mmx1¼ 42mmx1½		SAN6 6243 Reducer Insert 76x67mm 108x42mm 108x54mm 108x67mm 108x76mm		SAN24 6130 Tee Equal 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	
SAN3 8243G Male Adaptor 54mmx2 67mmx2½ 76mmx3 108mmx4		SAN12 6002A 90 Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		SAN25 6130 Tee Red Branch 22x15mm 42x22mm 28x15mm 28x22mm 35x22mm 35x28mm	

Sanha Copper Pressfittings upto 54mm can be crimped with any press-on clamps & crimping tools available in the market for metal crimp connections (Regular maintenance is absolutely necessary for all tool/clamps & calibration every 12 months)

Copper fittings to BS EN12449 gunmetal fittings to BS EN1982.

Copper pipe to correspond to EN1057 or BS2871

Max temp 120C max pressure PN16, for indication only see manufacturers temp/pressure graph.

Sanha offer a full range of fittings for gas, solar heating (200C), compressed air, stainless steel material & valves including radiator, ball valves & manifolds.

Additional size fittings available please see Sanha full catalogue.

SYSTEM TECHNOLOGY OF SANHA

More Comfortable - Fairer - Safer

SANHA®

www.sanha.com

Copper Pressfittings 12mm – 108mm (Stock range shown)
WRAS/KIWA Approved. Suitable for Hot/Cold & Heating Services

SAN25 6130 Tee Red Branch 42x28mm 42x35mm 54x35mm 54x42mm 67x28mm		SAN27 6130 Red Tee 22x15x15mm 28x22x15mm 28x22x22mm		SAN69 8333G Male Union 15mmx1/2 22mmx3/4 28mmx1	
SAN25 6130 Tee Red Branch 67x35mm 67x42mm 67x54mm 76x42mm 76x54mm		SAN30 8130G BSP Branch Tee 15mmx1/2 22mmx1/2 22mmx3/4 28mmx1/2		SAN69 8333G Male Union 35mmx1 1/4 42mmx1 1/2 54mmx2	
SAN25 6130 Tee Red Branch 76x67mm 108x54mm 108x67mm 108x76mm		SAN30 8130G BSP Branch Tee 35mmx1/2 42mmx1/2 54mmx1/2		SAN1F RGPf Flange PN10/16 28mm 76mm 35mm 108mm 42mm 54mm 67mm	
SAN26 6130 One End Red Tee 22x15x22mm 28x22x28mm		SAN61 6301 End Cap 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		SAN7 8246G F/I BSP Insert 15mmx1/2 54mmx2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2	

SANHA®-Press – - the all rounder



SANHA® System press fittings	Operational temperature
SANHA®-Press system fitting with EPDM gasket	-30 °C – +120 °C
SANHA®-Press Gas system fittings with HNBR gasket	-20 °C – +70 °C
SANHA®-Press Solar system fittings with FKM gasket	-20 °C – +200 °C (depending on the medium)
Type of threading: Connecting thread: R/Rp thread according to EN 10226 Fastening screw thread: G thread according to EN/ISO 228	

Carbon Steel Nirotherm Pressfittings 15-108mm (Stock range shown)
Suitable For Hot/Cold Water, Heating, Clean Air Systems & Industrial Applications

SC1 24270 Straight Coupling 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm		SC6 24243 Reducer Insert 42x22mm 42x28mm 42x35mm 54x35mm 54x42mm		SC21s 24040 45 Str Elbow m/f 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm	
SC2 24240 Female Adaptor 15mmx1/2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2		SC6 24243 Reducer Insert 76x35mm 76x42mm 76x54mm 89x54mm 89x42mm		SC24 24130 Tee Equal 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm	
SC2 24240 Female Adaptor 54mmx2 76mmx2 1/2 89mmx3		SC6 24243 Reducer Insert 108x42mm 108x54mm 108x76mm 108x89mm		SC25 24130 Red Branch Tee 22x15mm 28x15mm 28x22mm 35x22mm 35x28mm	
SC3 24243G Male Adaptor 15mmx1/2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2		SC12 24002A 90 Elbow 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm		SC25 24130 Red Branch Tee 42x22mm 42x28mm 42x35mm 54x35mm 54x42mm	
SC3 24243G Male Adaptor 54mmx2 76mmx2 1/2 89mmx3		SC12s 24001A 90 Str Elbow m/f 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm		SC25 24130 Red Branch Tee 76x35mm 76x42mm 76x54mm 89x54mm 89x76mm	
SC6 24243 Reducer Insert 22x15mm 28x15mm 28x22mm 35x22mm 35x28mm		SC21 24041 45 Elbow 15mm 42mm 18mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm		SC25 24130 Red Branch Tee 108x54mm 108x76mm 108x89mm	

SANHA®-Therm – - the most extensive assortment

SANHA®-Therm system fittings are particularly economic alternative to closed systems such as heating and solar plants, as well as compressed air and cooling system applications.

SANHA®-Therm system fittings (series 24000)

Shaped part gasket EPDM. **SANHA®-Therm** fittings are marked with a red dot. They are optimally applicable with **SANHA®-Therm** system pipes (compare table p. 18/19).

SANHA®-Therm system pipes of C steel (series 24000)

from d = 12 mm to d = 108 mm

Un-alloyed steel, Material no. 1.0034 (E 195) according to EN 10305, outside zinc plated for the optimal protection from outside corrosion.



Carbon Steel Nirotherm Pressfitting 15-108mm (Stock range shown)
Suitable for Hot/Cold Water, Heating, Clean Air Systems & Industrial Applications

SC26 24130 One Red Tee 22x15x22mm 28x22x28mm 35x28x35mm		SC1F 243TPF Flange PN10/16 76mm-dn65 89mm-dn80 108mm-dn100		SC1M 24000 Slip Coupling 15mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm 42mm	
SC27 24130 Reduced Tee 22x15x15mm 28x22x15mm 28x22x22mm 35x28x22mm 35x28x28mm		SC61 24301 End Cap 15mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm 42mm		SC7 24246 Female Bsp Insert 15mmx1/2 22mmx3/4	
SC30 3413G Bsp Branch Tee 15mmx1/2 22mmx1/2 28mmx1/2 28mmx3/4		SC69 M24330 Male Union 15mmx1/2 22mmx3/4 28mmx1		SC11 24246 Union Flat Seat 15mm 22mm 28mm 35mm 54mm	
SC30 3413G Bsp Branch Tee 35mmx1/2 42mmx1/2 54mmx1/2		SC69 M24330 Male Union 35mmx1 1/4 42mmx1 1/2 54mmx2		Tube 24000 6 Mtr Lengths 15mm 54mm 22mm 76mm 28mm 89mm 35mm 108mm 42mm	

Sanha Carbon Steel Fittings up to 54mm can be crimped with pressing tools & jaws provided for metal connection type M-MM (Please check with Sanha for tool suitability)

Nirotherm tube to Din EN10088, fittings to CW024A/CW617N

Max Temp 120C, Max Pressure PN16 (for indication only please check with manufacturers temp/pressure graph)

The economic alternative for closed systems

SANHA®-Therm offers a complete pipe and fitting assortment in the proven SANHA quality for diameters from 12 to 108 mm. The electro galvanising offers secure protection against external corrosion for many decades

Operating conditions for SANHA®-Therm press connections

Pipe outside diameter	Operating pressure
Water and aqueous solutions	
d ≤ 108 mm	16 bar
Technical gases (non-toxic, inflammable)	
d ≤ 108 mm	16 bar

SANHA® System press fittings	Operational temperature
SANHA®-Therm system fitting with EPDM gasket	-30 °C – +120 °C

Type of threading:
Connecting thread: R/Rp thread according to EN 10226
Fastening screw thread: G thread according to EN/ISO 228

Yorkshire Potable integral solder ring fittings 6mm-108mm manufactured to BS EN1254 Part1

YP1 Straight Coupling 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		YP6 Reducer Insert 15x8mm 35x15mm 15x10mm 35x22mm 22x15mm 35x38mm 28x15mm 42x15mm 28x22mm 42x22mm		YP24 Tee 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	
YP1 IM Imp/Metric Coup 1/2x15mm 3/4x22mm 1x28mm 1 1/4x35mm 1 1/2x42mm		YP6 Reducer Insert 42x28mm 54x35mm 42x35mm 54x42mm 54x15mm 67x35mm 54x22mm 67x42mm 54x28mm 67x54mm		YP25 Tee Red branch 22x15mm 35x15mm 22x28mm 35x22mm 28x15mm 35x38mm 28x22mm 42x15mm 28x35mm 42x22mm	
YP1R Reducing Coup 15x8mm 42x28mm 22x15mm 42x35mm 28x15mm 54x35mm 28x22mm 54x42mm 35x22mm		YP12 Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		YP25 Tee Red branch 42x28mm 54x35mm 42x35mm 54x42mm 54x15mm 67x28mm 54x22mm 76x42mm 54x28mm 76x54mm	
YP2 Female Conn 15mmx1/4 54mmx2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2		YP12S Street Elbow M/F 15mm 42mm 22mm 54mm 28mm 67mm 35mm 76mm		YP26 TEE One End Reduced 22x15x22 35x28x28 28x15x28 42x15x42 28x22x28 42x22x42 35x15x35 42x28x42 35x22x35 42x35x42	
YP3 Male Conn 15mmx1/2 54mmx2 22mmx3/4 76mmx3 28mmx1 108mmx4 35mmx1 1/4 42mmx1 1/2		YP15 Backplate Elbow 15mmx1/2 22mmx3/4		YP26 TEE One End Reduced 54x42x54mm 67x54x67mm 76x42x76mm 76x54x76mm	
YP3LC Male Red Conn 15mmx1/4 15mmx3/8 22mmx1/2 28mmx3/4		YP21 Obtuse Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		YP27 TEE End/Branch Red 22x15x15mm 28x15x15mm 28x15x22mm 28x22x15mm 28x22x22mm	
YP5 Tank Connector 15mmx1/2 54mmx2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2		YP21S 45 M/F Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		YP27 TEE End/Branch Red 35x22x22mm 35x28x15mm 35x28x22mm 35x28x28mm	

We stock from 6mm-108mm, some large 76/108mm fittings are made from gunmetal with wedge ring design.

Yorkshire potable integral solder ring fittings 6mm-108mm manufactured to BS EN1254 Part1

YP27 TEE End/Branch Red 42x28x28mm 42x35x28mm 42x35x35mm 54x42x42mm		YP61 Stop End 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		YP69 Male Union 15mmx1/2 54mmx2 22mmx3/4 76mmx3 28mmx1 108mmx4 35mmx1 1/4 42mmx1 1/2	
YP28 TEE Both ends Red 8x15mm 35x42mm 15x22mm 42x54mm 15x28mm 22x28mm 28x35mm		YP62 Tap Connector 15mmx1/2 15mmx3/4 22mmx1/2 22mmx3/4		YP69 F Female Union 15mmx1/2 54mmx2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2	
YP29 TEE One End BSP 15x1/2x15mm 22x3/4x22mm 28x1x28mm		YP63 Bent Tap Conn 15mmx1/2 22mmx1/2 22mmx3/4		YP415GM Gate Valve 15mm 35mm 22mm 42mm 28mm 54mm	
YP29R TEE Red End BSP 22x1/2x22mm 28x3/4x28mm 28x1x28mm 35x1x35mm		YP65 Bent M/Union 15mmx1/2 54mmx2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2		YP151 LS L/S Gate Valve 15mm 35mm 22mm 42mm 28mm 54mm	
YP30 TEE Fem BSP Branch 15mmx1/2 22mmx3/4 28mmx1		YP65F Bent Fem/Union 15mmx1/2 54mmx2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2		YP501 Stopcock 15mm 35mm 22mm 42mm 28mm 54mm	
YP30R TEE Fem BSP Branch 22mmx1/2 42mmx1/2 28mmx1/2 28mmx3/4 35mmx1/2 35mmx3/4					

Yorkshire offer additional fittings & sizes to the above, please ask for full product guide.

Yorkshire potable fittings are also available in chrome plated, general high duty & waste.



Each Yorkshire fitting contains the correct amount of lead-free solder to make a strong reliable joint without the need for additional solder. Fittings are manufactured from copper or copper alloys to EN 1254. With over 600 items including line fittings, valves, heating components, waste fittings and traps, the range is one of the most extensive available.

- Available in sizes 6 to 67mm
- For use on potable water applications
- Compatible with copper tube
- WRAS approved with 25 year guarantee

 Pegler Yorkshire



www.pegler-yorkshire.co.uk

The Push Fit Jointing System Manufactured From DZR Copper Alloy To EN1254

T1 Straight Coupling 15mm 22mm 28mm		T21 Obtuse Elbow 15mm 22mm 28mm		T30 Tee Female Bsp 15mmx1/2 22mmx3/4 28mmx1	
T2 Female Conn 15mmx1/2 22mmx3/4 22mmx1 28mmx1		T24 Tee 15mm 22mm 28mm		T61 Stop End 15mm 22mm 28mm	
T3 Male Conn 15mmx1/2 22mmx3/4 22mmx1 28mmx1		T25 Tee Red branch 22x15mm 28x15mm 28x22mm		T62 Straight Tap Connector 15mmx1/2 15mmx3/4 22mmx3/4	
T6 Reducer 22x15mm 28x15mm 28x22mm		T26 Tee One End Reduced 22x15x22mm 28x15x28mm 28x22x28mm		T62 Bent Tap Connector 15mmx1/2 22mmx3/4	
T12 Elbow 15mm 22mm 28mm		T27 Tee End/Branch Red 22x15x15mm 28x22x22mm		TF92 Flex Tap Conn 15mmx1/2 22mmx3/4	
T15 Back Plate Elbow 15mmx1/2		TP501 Barrier Pipe 15x3mtr 28x3mtr 15x6mtr 28x6mtr 22x3mtr 22x6mtr		TP515 Barrier Pipe Coils 15x25mtr 28x25mtr 15x50mtr 28x50mtr 22x25mtr 22x50mtr	

A full range from 10mm to 54mm is available in stainless steel.

Tectite is designed to push together in seconds creating a perfect heat free installation joint. Ideal for jointing copper & chrome plated tube to BS EN1257 PEX and PB plastic pipe.

Tectite fittings are WRAS approved for use on hot & cold water services & heating.

NOT FOR USE ON GAS.

Tectite
CLASSIC

Fittings simply push together in seconds to create a perfect joint. This heat-free technique offers substantial installed cost savings, eliminates the need for hot works permits and heavy, expensive tools.

- Demountable fittings in sizes 10mm to 28mm
- Compatible with copper tube and PEX pipe
- WRAS approved with 30 year System Guarantee



Pegler Yorkshire

AI
Adaptive
Industries



www.pegleryorkshire.co.uk

Endex range of end feed capillary fittings 6mm to 219mm manufactured to BS EN1254 Part 1

N1 Straight Coupling 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		N6 Reducer Insert 42x28mm 54x35mm 42x35mm 54x42mm 54x15mm 67x28mm 54x22mm 67x35mm 54x28mm 67x42mm		N21 Obtuse Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	
N1R Reducing Coup 15x10mm 42x22mm 22x15mm 42x28mm 28x15mm 42x35mm 28x22mm 52x42mm 35x28mm		N6 Reducer Insert 76x35mm 76x42mm 76x54mm 76x67mm		N21S 45 Str Elbow M/F 15mm 35mm 22mm 42mm 28mm 54mm	
N1 SLIP Coupling 15mm 35mm 22mm 42mm 28mm 54mm		N6 Reducer Insert 108x42mm 108x54mm 108x67mm 108x76mm		N24 Tee 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm	
N2 Female Conn 15mmx1/2 42mmx1/2 22mmx3/4 54mmx2 28mmx1 35mmx1 1/4		N7 Female Adaptor 15mmx1/2 54mmx2 22mmx3/4 28mmx1 35mmx1 1/4 42mmx1 1/2		N25 Tee Red Branch 22x15mm 35x28mm 28x15mm 42x15mm 28x22mm 42x22mm 35x15mm 42x28mm 35x22mm	
N3 Male Conn 15mmx1/2 54mmx2 22mmx3/4 67mmx2 1/2 28mmx1 76mmx3 35mmx1 1/4 108mmx4 42mmx1 1/2		N12 Elbow 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		N25 Tee Red Branch 42x35mm 54x42mm 54x15mm 67x28mm 54x22mm 76x35mm 54x28mm 76x42mm 54x35mm 76x54mm	
N5 Tank Connector 15mmx1/2 22mmx3/4 28mmx1		N12s Street Elbow M/F 15mm 35mm 22mm 42mm 28mm 54mm		N26 TEE One End Reduced 22x15x22 35x28x35 28x15x28 42x35x42 28x22x28 54x35x54 35x15x35 54x42x54 35x22x35	
N6 Reducer Insert 15x8mm 35x15mm 15x10mm 35x22mm 22x15mm 35x28mm 28x15mm 42x15mm 28x22mm 42x22mm		N15 Backplate Elbow 15mmx1/2 22mmx3/4		N27 TEE End/Branch Red 22x15x15mm 28x15x15mm 28x15x22mm 28x22x15mm 28x22x22mm	

Above items are for indication only other sizes available on request.

Endex range of end feed capillary fittings 6mm to 219mm manufactured to BS EN1254 Part 1

N27 TEE End/Branch Red 35x22x22mm 35x28x15mm 35x28x22mm 35x28x28mm		N29R TEE Red End BSP 22x ¹ / ₂ x22mm 28x ¹ / ₂ x28mm 28x ³ / ₄ x28mm		N62 Tap Connector 15mmx ¹ / ₂ 15mmx ³ / ₄ 22mmx ³ / ₄	
N27 TEE End/Branch Red 42x28x28mm 42x35x28mm 42x35x35mm 54x42x42mm		N30 TEE Fem Branch BSP 15mmx ¹ / ₂ 22mmx ³ / ₄ 28mmx1		N63 Bent Tap Conn 15mmx ¹ / ₂ 15mmx ³ / ₄ 22mmx ³ / ₄	
N28 TEE Both Ends Red 15x22mm 15x28mm 22x28mm 28x35mm 35x42mm		N30R TEE Fem Branch BSP 22mmx ¹ / ₂ 28mmx ¹ / ₂ 28mmx ³ / ₄		N65 Bent M/Union 15mmx ¹ / ₂ 54mmx2 22mmx ³ / ₄ 28mmx1 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂	
N29 TEE One End BSP 15x ¹ / ₂ x15mm 22x ³ / ₄ x22mm 22x ¹ / ₂ x22mm		N61 Stop End 15mm 54mm 22mm 67mm 28mm 76mm 35mm 108mm 42mm		N69 Male Union 15mmx ¹ / ₂ 54mmx2 22mmx ³ / ₄ 28mmx1 35mmx1 ¹ / ₄ 42mmx1 ¹ / ₂	

ENDEX

Capillary fittings that are light and easy to handle simple to install by applying heat from a blow torch & solder to the mouth of the fitting.

- Sizes from 6mm to 54mm for use with soft or hard solder sizes from 67mm to 159mm for use with high temperature brazing alloys
- Manufactured from copper, gunmetal or DZR to EN 1254
- WRAS approved with 25 year guarantee

 Pegler Yorkshire

AI
Aalberts
Industries




www.pegleryorkshire.co.uk

Brass compression fittings BS EN1254-2, 6mm-108mm (stock range shown)
Additional fittings available to order

610 Straight Coupling 6mm 28mm 8mm 35mm 10mm 42mm 15mm 22mm		611TC BSPP Tank Coupling 42mmx1½ 54mmx2 67mmx2½ 76mmx3		616 BSPT Male Elbow 22mmx¾ 22mmx1 28mmx1	
610 Straight Coupling 54mm 67mm 76mm 108mm		612 BSPP Female Coupling 8mmx¼ 10mmx¼ 10mmx⅜ 15mmx½ 15mmx¾		616 BSPT Male Elbow 35mmx1¼ 42mmx1½ 54mmx2 67mmx2½	
611 BSPT Male Coupling 6mmx⅛ 6mmx¼ 8mmx¼ 10mmx¼ 10mmx⅜		612 BSPP Female Coupling 22mmx¾ 22mmx1 28mmx1		617 BSPP Female Elbow 8mmx¼ 28mmx1 10mmx⅜ 15mmx½ 22mmx¾ 22mmx1	
611 BSPT Male Coupling 15mmx½ 15mmx¾ 22mmx¾ 22mmx1 28mmx1		612 BSPP Female Coupling 35mmx1¼ 42mmx1½ 54mmx2 67mmx2½ 76mmx3		617 BSPP Female Elbow 35mmx1¼ 42mmx1½ 54mmx2	
611 BSPT Male Coupling 15mmx⅜ 22mmx½ 28mmx¾ 35mmx1 35mmx1¼		615 Elbow 6mm 28mm 8mm 10mm 15mm 22mm		617W BSPP Blackplate Elbow 15mmx½ 15mmx¾ 22mmx½ 22mmx¾	
611 BSPT Male Coupling 42mmx1½ 54mmx2 67mmx2½ 76mmx3 108mmx4		615 Elbow 35mm 108mm 42mm 54mm 67mm 76mm		618 Tee 6mm 8mm 10mm 15mm 22mm	
611TC BSPP Tank Coupling 15mmx½ 22mmx¾ 28mmx1 35mmx1¼		616 BSPT Male Elbow 8mmx¼ 10mmx⅜ 15mmx½ 15mmx¾		618 Tee 28mm 76mm 35mm 108mm 42mm 54mm 67mm	

Brass compression Fittings BS EN1254-2, 6mm-108mm (stock range shown)
Additional fittings available to order

618B Tee Red Branch 22x15mm 28x15mm 28x22mm 35x15mm 35x22mm		630 Tee BSP Branch 15mmx $\frac{1}{2}$ 22mmx $\frac{1}{2}$ 22mmx $\frac{3}{4}$ 28mmx $\frac{1}{2}$ 28mmx1		651 Stop End 15mm 22mm 28mm 35mm	
618B Tee Red Branch 35x28mm 42x22mm 42x28mm 42x35mm 54x28mm		648 Reducing Set 8x6mm 10x6mm 10x8mm 15x8mm		651 Stop End 42mm 54mm 67mm 76mm 108mm	
618B Tee Red Branch 67x28mm 67x35mm 67x42mm 67x54mm		648 Reducing Set 15x12mm 22x15mm 28x15mm 28x22mm 35x15mm		637 Straight Wash/Mch Valve 15mmx $\frac{3}{4}$ 637 Angle 15mmx $\frac{3}{4}$	
626 Straight Tap Conn 15mmx $\frac{1}{2}$ 15mmx $\frac{3}{4}$ 22mmx $\frac{1}{2}$ 22mmx $\frac{3}{4}$		648 Reducing Set 35x22mm 35x28mm 42x15mm 42x22mm 42x28mm		678B Olive 6mm 28mm 8mm 35mm 10mm 42mm 15mm 54mm 22mm 67mm	
627 Bent Tap Conn 15mmx $\frac{1}{2}$ 22mmx $\frac{1}{2}$ 22mmx $\frac{3}{4}$		648 Reducing Set 42x35mm 54x42mm 54x15mm 54x22mm 54x28mm 54x35mm		678C Imperial Olive 22mmx $\frac{3}{4}$ 35mmx1 $\frac{1}{4}$ 42mmx1 $\frac{1}{2}$ 15mmx54mm same olive	

DZR compression fittings to BS EN1254-2 are available to order & should be specified when water conditions are such that standard brass fittings may suffer corrosion.

Compression ranges available in metric MDPE, copper/chrome waste fittings & traps.

KUTERLITE

Easy to assemble Kuterlite compression fittings are simple and reliable mechanical joints that can be broken and re-made with the use of spanners. Kuterlite fittings are available in both Brass and DZR to EN 1254 Part 2.

- Available in sizes 6 to 108mm
- Compatible with copper tube and on sizes up to 28mm with carbon steel and stainless steel tube, PEX and PB pipe
- WRAS approved with 25 year guarantee

 Pegler Yorkshire

AI
Alberts
Industries



www.pegleryorkshire.co.uk

CHROME PLATED BRASS COMPRESSION FITTINGS BS EN1254-2

STOCK SIZES SHOWN. 6mm-54mm AVAILABLE & POLISHED CHROME TO SPECIAL ORDER

610CP Straight Coupling 15mm 22mm 28mm		616CP Male Elbow 15mmx1/2 22mmx3/4 22mmx1 28mmx1		627CP Bent Tap Conn 15mmx1/2 22mmx3/4	
611CP Male Coupling 15mmx1/2 22mmx3/4 28mmx1		617CP Female Elbow 15mmx1/2 22mmx3/4 28mmx1		651CP Stop End 15mm 22mm 28mm	
612CP Female Coupling 15mmx1/2 22mmx3/4 28mmx1		618CP Tee 15mm 22mm 28mm		617WCP Female B/Plate 15mmx1/2 22mmx3/4	
615CP Elbow 15mm 22mm 28mm		618CP Tee Red Branch 22x15mm 28x15mm 28x22mm		648CP Reducing Set 22x15mm 28x22mm	

TUBE SIZE	PART No
15mm	TB240
22mm	TB241
28mm	TB242
35mm	TB243
42mm	TB244
54mm	TB245

**WE STOCK TUBE SIZES FROM
15mm-54mm**

**CHROME PLATED COPPER
TUBE EN1057 IN 3MTR LTHS**

