



JKL PART NUMBER	LENGTH A +/- 2mm	COLOR	STARTING CIRCUIT VOLTAGE VS (Vrms)	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m2)	*RATED LIFE (HRS)
BF350-20B	50mm	RGB HIGH OUTPUT WHITE 5400° KELVIN (REF.)	500	195	5 ± 1	28000 ± 2800	20,000
BF375-20B	75mm		525	210	5 ± 1	28000 ± 2800	20,000
BF386-20B	86mm		540	220	5 ± 1	28000 ± 2800	20,000
BF3100-20B	100mm		665	270	5 ± 1	28000 ± 2800	20,000
BF3115-20B	115mm		685	287	5 ± 1	28000 ± 2800	20,000
BF3130-20B	130mm		705	305	5 ± 1	28000 ± 2800	20,000
BF3160-20B	160mm		850	345	5 ± 1	28000 ± 2800	20,000
BF3180-20B	180mm		940	380	5 ± 1	28000 ± 2800	20,000
BF3216-20B	216mm		1100	440	5 ± 1	28000 ± 2800	20,000
BF3240-20B	240mm		1150	480	5 ± 1	28000 ± 2800	20,000
BF3250-20B	250mm		1200	520	5 ± 1	28000 ± 2800	20,000
BF3275-20B	275mm		1275	593	5 ± 1	28000 ± 2800	20,000
BF3300-20B	300mm		1350	665	5 ± 1	28000 ± 2800	20,000
BF3360-20B	360mm		1500	785	5 ± 1	28000 ± 2800	20,000
BF3380-20B	380mm		1590	825	5 ± 1	28000 ± 2800	20,000

*NOTE: RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			METRIC  THIRD ANGLE PROJECTION		DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0.2 2 PL +/- 0.20 ANGLE +/- 0		JKL COMPONENTS CORPORATION					
							TITLE					
							MINIATURE COLD CATHODE FLUORESCENT LAMP					
F			ADD PART NUMBER BF3115-20B		12/19/02		SIZE		FSCM NO.		DRAWING NO.	
E			ADD PART NUMBER BF3180-20B & BF3380-20B		11/30/01		A		55335		BF 3-20B	
D			ADD PART NUMBER BF3240-20B		4/26/01							
C			ADD PART NUMBER BF3130-20B		9/11/00							
B			ADD PART NUMBER BF375-20B		4/21/00							
A			LENGTH ±5 TO ±2		2/25/00							
			RELEASED - CANCEL BF-3mm DIA DRAWING		2/21/00							
REV. NO.			DESCRIPTION/ECO NUMBER		APPV'D DATE		SCALE		RELEASED DATE		REVISION DATE	
							NONE		2/21/00		12/19/02	
											REV. NO. F	
											SHEET 1 OF 1	
			</									

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF3160-20B](#)