

4		3		2		1			
THIS DRAWING IS UNPUBLISHED.				RELEASED FOR PUBLICATION ,19 .					
© COPYRIGHT 19				BY AMP INCORPORATED. ALL RIGHTS RESERVED.					
LOC		DIST		REVISIONS					
G		14		P	LTR	DESCRIPTION	DATE	DWN	APVD
				N		REV / REDRAWN / 0720-0482-95 & 0720-0002-95	14FEB95	LO	ME

BODY

INSULATION

13.08
[.515] MAX

1. USE FOR AN UNSTRIPPED (SINGLE) WIRE END ONLY

2. WIRE INSUL DIA, 3.81-5.33 [.150-.210]

-	-	-
-	-	-
1000	LOOSE PIECE	324487
QTY	PACKAGE TYPE	PART NO

AMP INCORPORATED CUSTOMER SERVICE SYSTEM		MAX RECOMMENDED OPERATING TEMPERATURE: 105°C [221°F]	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN L OLMEDA 14FEB95	AMP Incorporated				
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		DIMENSIONS: mm [in]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±- 1 PLC ±- 2 PLC ±0.20 [.008] 3 PLC ±- 4 PLC ±- ANGLES ±- FINISH BODY, TIN PLATE PER MIL-T-10727	CHK M ELLIS 14FEB95	Harrisburg, PA 17105-3608			
	FOR APPLICATION TOOLING INFORMATION					TOOLING ASSISTANCE CENTER 1-800-722-1111	APVD T MICHIELUTTI 14FEB95	NAME		
						FOR ORDER ENTRY 1-800-526-5142	PRODUCT SPEC -	SPARE WIRE CAP, YELLOW		
		CIRCULAR MIL AREA: -	MATERIAL BODY, CU PER ASTM B152 INSUL, NYLON, COLOR, YELLOW		APPLICATION SPEC -	SIZE A3	CAGE CODE 00779	DRAWING NO C-324487		
					WEIGHT -	SCALE 8:1				
					CUSTOMER DRAWING	SHEET 1 OF 1				
						REV N				