


**Sales Outline Drawing****Revision A****Specifications:**

|                                |                                                |
|--------------------------------|------------------------------------------------|
| Resonant Frequency (Hz)        | 400 ± 100                                      |
| Operating Voltage (Vdc)        | 4.0 ~ 8.0                                      |
| Rated Voltage (Vdc)            | 6.0                                            |
| Current Consumption Max. (mA)  | 30 at Rated Voltage                            |
| Sound Pressure Level Min. (dB) | 85 at 10cm at Rated Voltage                    |
| Tone/Pulse Rate                | Constant                                       |
| Operating Temperature (°C)     | -20 ~ +70                                      |
| Storage Temperature (°C)       | -30 ~ +80                                      |
| Housing                        | ABS 757 UL94HB plastic resin<br>(Color: Black) |
| Leading Wire                   | 26 AWG                                         |
| Weight (Grams)                 | 8.0                                            |
| Options                        | For other options contact factory              |

**RoHS Compliant****Dimensions:** (units: mm)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mallory Sonalert:](#)

[PK-16N04WA-06Q](#)