

**Series EM2218**

Header with Flanges; (Mates with EM2118, EM3118 Series); 5.08 Centers

**SPECIFICATIONS:**

**Rating:** 12A, 300V

**Center Spacing:** 0.20" (5.08mm)

**Housing Material:** UL rated 94V0 Thermoplastic




**Contact Material:** Tin-Plated Brass

**Operating Temperature:** 105°C (221°F) max., -55°C (-67°F) min.

**Recommended PCB Hole Diameters:** 0.059" (1.50mm)

**Construction:** Mold-to-Length

**Agency Information:**  File E62622; CE Certified

**EM221804H****EM221804V****Dimensions - in (mm)****HORIZONTAL****VERTICAL****Part Numbering System**

Inches (Millimeters)

**Series****EM2218****# of Poles****02 to 22****Orientation****H - Horizontal****V - Vertical**

**Mating Plugs:** EM2118 pg. 96  
EM3118 pg. 97