


SPECIFICATIONS

Model Number: JQ48B4
 Part Number: 19031091A

August 8, 2005



Mechanical Drawing:



Motor:

Nominal Voltage	= 48 vdc
Operating Voltage Range	= 24 - 56 vdc
Nominal Running Current	= 0.460 amps
Locked Rotor Current	= 1.00 amps
Running Power	= 22.0 watts
Average Speed	= 3475 rpm
Bearings	= Ball
Air Flow	= 235 cfm
Acoustic:	= 54.3 dBA

Construction:

Venturi: Die-Cast Aluminum, Black
 Propeller: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 75,000 hours at 40°C.

Additional Features:

Brushless DC Motor	
Locked Rotor Protection	
Polarity Protected	
Automatic Restart Capability	
Operating Temperature:	-10°C to 70°C
Storage Temperature:	-40°C to 85°C

Termination:

2 blade terminals

Agency Approvals:

UL, cUL, CE