





PART NUMBER	ITEM ① BODY	ITEM ② BASE	ITEM ③ CRIMP SLEEVE
142-0004-3D1	BRASS GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN	BRASS GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN	COPPER GOLD PL .00001 MIN OVER NICKEL PL .00005 MIN OVER COPPER PL .00005 MIN
142-0004-3D6	BRASS NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN	BRASS NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN	COPPER NICKEL PL .0001 MIN OVER COPPER PL .00005 MIN



- NOTES:
- SPECIFICATIONS:
CABLE ACCEPTABILITY: RG 316/U DOUBLE SHIELDED
RG 188/U DOUBLE SHIELDED
CABLE HEX CRIMP SIZE: .151
CABLE RETENTION: 20 LBS MIN OR CABLE BREAKING STRENGTH



CABLE STRIP DIMENSIONS



MOUNTING HOLE LAYOUT

DRAWING NO.									
C - 142-0004-301/310									
0	REVISIONS								
ENGINEERING RELEASE									
1	6-12-92	R	H	A	K				ECO 41080

CUSTOMER DRAWING

THIS DRAWING TO BE INTERPRETED
PER ANSI Y 14.5M - 1982

"μSTATION"

COMPANY CONFIDENTIAL

TOLERANCE UNLESS OTHERWISE SPECIFIED		DRAWN BY VET	DATE 5-8-92	 Cinch Connectivity Solutions 299 Johnson Ave. Ste. 100 Worcester, MA 01605 1-800-247-8256	
DECIMALS .XX	mm	CHECKED BY	DATE		
.XXX		APPROVED BY VET	DATE 6-15-92	TITLE CABLE TERMINATION, RA PC MOUNT RG 316 DOUBLE SHIELDED	
MATL		APPROVED BY TAK/RJB	DATE 6-15-92	CODE NO.	DRAWING NO. C - 142-0004-301/310
FINISH		RELEASE DATE		SCALE 10:1	U/M INCH SHEET 2 OF 2