




LOC	DIST	P	F	ZONE	LTR	REVISIONS		
						DESCRIPTION	DATE	APPD
	BD	26			O	RLSE NPR 2275 WAS 88-4837-17	01/05/88	-
					A	REVISED ECN-BD2959	05/09/89	-
					B	REVISED ECN BD3043	06/20/88	RW
					C	REVISED ECN-BD3213	8-16-89	RW
					D	REV PER ECN BD5426	10/28/91	-
					E	REV PER EC 0020-824-95	12 OCT 95	JH
					F	REV PER EC 0410-95-96	01 MAR 97	JGH
					G	REV PER EC 0410-281-97	28 SEP 97	JGH
					H	REV PER EC 0410-410-97	05 FEB 98	JGH






SECTION Z-Z
SCALE 10:1





DETAIL D
4 PIN FACE

- 1 RECEPTACLE CONTACTS: COPPER ALLOY.
RECEPTACLE SHIELD: COPPER ALLOY.
HOUSING: THERMOPLASTIC, BLACK, 94V-0 RATED.
- 2 PLATING:
RECEPTACLE CONTACTS - GOLD FLASH PLATED ON MATING END, TIN-LEAD PLATED .0030 MIN [0.00120 MIN] THICK ON SOLDER TAIL ALL OVER .0013 MIN [0.00050 MIN] THICK NICKEL.
- 3 PLATING:
SHIELD: 1.50-4.00µm[0.000059-.000158] THICK BRIGHT TIN.
4. RECEPTACLE ASSEMBLY MATES WITH 4 PIN 9.00±.10 [0.354±.004] DIAMETER PLUG.
- 5 DATUMS AND BASIC DIMENSION SUPPLIED BY CUSTOMER.



4 PIN PCB LAYOUT
BOTTOM VIEW



DETAIL C
SCALE 50:1

749230-1					
PART NO					
DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON : 2 PLC DEC ± - 3 PLC DEC ± 0.381 [0.015] ANGLES ± 0°30'			DR 1-24-89 P.COSMOS CHK 1-24-89 C.OHL APPD 1-24-89 B.H.MOSSER APPD 1-24-89 E.C.MYERS PRODUCT SPEC 108-1225		
MATERIAL			NAME		
FINISH			RECEPTACLE ASSY W/HOLD DOWN, 4 POS, RIGHT ANGLE, MINIATURE CIRCULAR DIN		
WEIGHT			SIZE D	FSCM NO 00779	DRAWING NO 749230
			SCALE 5:1	SHEET 1 OF 1	