

Item # LC1D18Q7, TeSys D IEC Contactor - 18A - Vac Coil

TeSys D IEC Contactor - 18A - Vac Coil

TeSys D IEC Contactor - 18A - 380Vac Coil



SPECIFICATIONS

Termination Method	Screw Clamp
Contact Rating	600V / 18A
Coil Voltage	380Vac 50/60 Hz
50/60 Hz Voltage Code	Q7
Coil Consumption Inrush	70 VA
Coil Consumption Sealed	7.5 VA
Power Wire Size	#10 - #18 AWG
Power Terminal Torque	15 lb-in (1.7 Nm)
Control Wire Size	#10 - #18 AWG
Control Terminal Torque	15 lb-in (1.7 Nm)
Mounting Hardware	35mm DIN Rail, #8 screw
Weight	0.73 lb (0.33 kg)
AC1 Resistive Rating	32 Amp
AC3 Inductive Rating	18 Amp
AC3 Single Phase 115V	1 HP
AC3 Single Phase 230V	3 HP

AC3 Three Phase 200V	5 HP
AC3 Three Phase 230V	5 HP
AC3 Three Phase 460V	10 HP
AC3 Three Phase 575V	15 HP
Control Contact Rating (1NC/0NO)	A600
UL File/CCN	E164862 / NLDX
CSA File	LR43364 3211 04
Meets Standard	IEC 60647-4
CE	Yes
RoHS	Yes