

Indicator Lights Neon, LED and Incandescent Lamp

Colours and voltages:

	Neon	Available with Red, Amber, Green or Clear lenses 100/130V (marked 110V), 200/250V (marked 230V)
	LED - DC	Red, Yellow, Green, Blue, White 2.0/2.2V Resistors for other voltages available.
	LED - AC	Red, Yellow, Green, Blue, White 110-230V ac operation.
	Incandescent lamp	Available with Red, Amber, Green, Clear or Blue lenses 6V, 12/14V, 24/28V.

- ▶ Neon, LED, mains LED or filament lamp
- ▶ Bezel sizes from 6.7 to 16.3mm diameter
- ▶ Red, amber, green and clear lenses
- ▶ Red, yellow, green, blue and white LEDs
- ▶ Wide choice of styles









UL file E63363

Approvals shown for neon versions only





RoHS compliant

SERIES	MODEL	TERM	PANEL & °C	DIMENSIONS (mm)
NL Neon	2870 	WL 	 12.7	
LE LED (DC)		K 2.8 	 0.75-2.0	
LE LED (DC)		H 4.8 	 page 6	
LE LED (AC)		C 6.3 		
NL Neon	589 	WL 	 12.7	
LE LED (DC)		K 2.8 	 0.8-1.5	
LE LED (DC)		H 4.8 	 page 6	
LE LED (AC)		C 6.3 		
NL Neon	81 Chrome bezel 	WL 	 12.7	
LE LED (DC)		K 2.8 	 9.5	
LE LED (DC)		H 4.8 	 page 6	
LE LED (AC)		C 6.3 		
FL Filament	177 Chrome bezel 	WL 	 12.7	
NL Neon		K 2.8 	 12.0max	
LE LED (DC)		H 4.8 	 page 6	
LE LED (AC)		C 6.3 		
FL Filament	67 Chrome bezel 	WL 	 12.7	
NL Neon		K 2.8 	 1.14max	
LE LED (DC)		H 4.8 	 page 6	
LE LED (AC)		C 6.3 		
FL Filament	180AA 	WL 	 12.7	
NL Neon		K 2.8 	 19.0max	
LE LED (DC)		H 4.8 	 page 6	
LE LED (AC)		C 6.3 		



▶ **ORDER FORMAT** **example**

▶ SERIES	▶ MODEL	▶ TERM	PANEL & °C	▶ DIMENSIONS (mm)
FL Filament NL Neon LE LED (DC)	180BB Chrome bezel 	WL  C 6.3 	 13.5  0.9-1.14  page 6	 
FL Filament NL Neon LE LED (DC) LE LED (AC)	579 	WL  K 2.8  H 4.8  C 6.3 	 14.0  2.5max  page 6	 
FL Filament NL Neon LE LED (DC) LE LED (AC)	392 	C 6.3 	 19.0  4.0max  page 6	