



⑩ 规格 Specifications

额定负荷 Ratings	DC 30 V 0.3 A
初期接触电阻 Initial Contact Resistance	30 mΩ Max.
绝缘电阻 Insulation Resistance	DC500 V 60 Sec. 100 MΩ Min.
抗电强度 Dielectric Voltage	AC 500 V (50~60HZ) 60 Sec.

操作力 Operating Force (gf)	A B B C C D D C C B B A
负荷寿命 Operating Life With Load	200±100 300±150 400±150

7	钢珠 STEEL BALL	STEEL	2	NATURAL
6	弹簧 SPRING	STEEL	1	NATURAL
5	端子 TERMINAL	C2680R ⑩	20	Ag PLATED
4	基板 TERMINAL BASE	PHENOL RESIN	1	YELLOW
3	接触片 CONTACT	C5210R ⑩	4	Ag CLAD
2	胶柄 KNOB	P O M	1	G 4 - 15
1	铁壳 FRAME	S P C C	1	Ni PLATED
序 NO.	零件 PART	材料 MATERIAL	数量 QTY	备注 REMARKS

A01	ADD: 规格 Specifications 见 ⑩	王光云	06-06-14
01	C2680R-EH → C2680R 见 ⑩	赖立辉	11 JUL 98
01	C5210R-EH/Ag CLAD → C5210R 见 ⑩	赖立辉	11 JUL 98
标号 REV	内容 DESCRIPTION	签名 SIGN.	日期 DATE
DWG NO.	ITEM1109		

TOLERANCES UNLESS OTHERWISE SPEC.	TITLE	SLIDE SWITCH	ITEM NO	SS-44D04-G
UNDER 1	± 0.10	DRAWN	王光云	06-06-14
1 - 10	± 0.30	REVIEWED	张念明	06-06-14
OVER 10	± 0.50	APPROVED	高洪	06-06-15
			PROJECTION	

COMAX ELECTRONICS (HUIZHOU) CO.,LTD.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[C&K Components:](#)

[SS-44D04-G 4](#)