

Modular Plugs

A complete variety of UL Recognized modular plugs are available. All plugs have 15 micro inches* of gold plating on the contacts standard applications for voice and data. Flat satin stranded, round stranded, and round solid cables are accommodated. Keyed, flat shielded and category 5 versions are available. Flat modular cable types are 28 AWG, 24 stranded. Round cable types accept 24 AWG, stranded or solid.

Part No.	RoHS	Description	Ty
300062		4P4C Handset Plug For Flat Satin, Stranded	—
300064		6P4C Plug For Flat Satin, Stranded	RJ11
300066		6P6C Plug For Flat Satin, Stranded	RJ12
300068		8P8C Plug For Flat Satin, Stranded	RJ45
300164		6P4C Plug For Round Twisted Pair, Solid	RJ11
300166		6P6C Plug For Round Twisted Pair, Solid	RJ12
300168		8P8C Plug For Round Twisted Pair, Solid	RJ45
300168K		8P8C Keyed Plug For Round Twisted Pair, Solid	RJ45
300160		DISCONTINUED	RJ50
300264		6P4C Plug For Round Twisted Pair, Stranded	RJ11
300266		6P6C Plug For Round Twisted Pair, Stranded	RJ12
300268		8P8C Plug For Round Twisted Pair, Stranded	RJ45
300066D		6P6C DEC Offset Plug For Flat Satin	MMJ
300068K		8P8C Keyed Plug For Round Twisted Pair, Stranded	RJ45
300068S		8P8C Shielded Plug For Round Twisted Pair, Solid	RJ45
300568		8P8C Category 5 Plug For Round Twisted Pair, Solid	RJ45
300566EZ		6P6C EZ RJ12 Plug (see below)	RJ12
300568EZ		8P8C EZ RJ45 Category 5 Plug (see below)	RJ45
300568L		8P8C Category 5 Liner Plug For Round Twisted Pair, Solid	RJ45
300568S		8P8C Shielded Category 5 Liner Plug For Round, Solid	RJ45
300668EZ		8P8C EZ RJ45 Category 6 Plug NEW (see below)	RJ45
300668SEZ		8P8C EZ RJ45 Shielded Category 6 Plug NEW (see below)	RJ45
CXB300EZ		Category 6 Boot with Strain Relief	Boot



EZ RJ45 Modular Plugs

The new patented **EZ-RJ45™** connector simplifies installation by allowing the pairs to be inserted through the connector. There is no handle liner or wire bar to deal with. Inspection of the correct conductor order is done before crimping so no connector is wasted wiring. The conductors are able to be pulled forward so the pairs are very close to the contacts. This method allows the integrity maintain Category Five, and even enhanced Category 5 and Category 6 capabilities. (50 u in. gold)
The EZRJ12™ and both EZRJ45™ can be crimped with most any standard tool, then trimmed with a cutter or small utility knife. H new BD45000 crimp tool crimps and trims the exposed conductors in one operation. The vertical action of the tool makes a uniform crimp.

PartNo.	RoHS	Description	
300566EZ		6P6C EZ-RJ12 Plug	RJ12
300568EZ		8P8C EZ-RJ45 Category 5 Plug (solid or stranded)	RJ45
300668EZ		8P8C EZ-RJ45 Category 6 Plug NEW (solid or stranded)	RJ45
300668SEZ		8P8C EZ-RJ45 Shielded Category 6 Plug NEW (solid or stranded)	RJ45
BD45000	-	Crimp and Trim Tool for EZ RJ12, EZ RJ45 Cat 5 & 6	----
BD45000BL	-	Replacement Blades (2 per Pkg) for BD45000 Tool	----
CXB300EZ	-	Cable Boot with Strain Relief (Required for Cat 6)	----
CXB500EZ	-	Cable Boot SNAGLESS Cat 5 (color: clear) NEW	----
CXB600EZ	-	Cable Boot SNAGLESS Cat 6 (color: clear) NEW	----

[Video Demo](#)



BD45000 Crimp & Trim Tool



EZ-RJ45 Cat 6
Shielded with
SNAGLESS Boot



CXB500/600
Snagless Boot

[Back to Index](#)

FOR TECHNICAL SUPPORT: PHONE 973-740-40 / FAX 973-347-2111

Category Five Liner Plugs

Category 5 Liner Plugs are supplied with an insertable liner for the conductors. This is also known as the **Wire Bar Style**. The separated conductors inserted into the liner, cut off squarely at bottom, inserted into the RJ45 plug, then perfectly crimped. (Use CBX300 series boots for 5 assembly).

Part No.	RoHS	Description	
300568L		8P8C Category 5 Liner Plug For Round Twisted Pair, Solid	RJ45
300568S		8P8C Shielded Category 5 Liner Plug For Round, Solid	RJ45



Wall Jacks

Plastic wall jacks are furnished with mounting hardware for easy installation. They are very economical and are to be used where not required. 15 micro inches of gold plate on the contacts is standard on all jacks. Rounded configuration, rear wiring terminals all to fit all standard receptacle boxes.

Part Number	RoHS	Description
300004IV		4C Ivory Flush Mount Single Jack, No UL
300004WH		4C White Flush Mount Single Jack, No UL
300006IV		6C Ivory Flush Mount Single Jack, No UL
300008IV		8C Ivory Flush Mount Single Jack, No UL
300014IV		4C Ivory Flush Mount Dual Jack, No UL
300014WH		4C White Flush Mount Dual Jack, No UL
300016IV		6C Ivory Flush Mount Dual Jack, No UL
300018IV		8C Ivory Flush Mount Dual Jack, No UL
300090		4C Ivory Wall Phone, 3 Jacks, No UL
300094IV		4C Ivory Wall Phone Jack, No UL
300094WH		4C White Wall Phone Jack, No UL
300095		4C Steel Wall Phone Jack, No UL
300104		4C Ivory Telephone/TV Jack, No UL
301004WH		4C Ivory Flush Mount Single Jack, UL
301006WH		6C Ivory Flush Mount Single Jack, UL
301008WH		8C Ivory Flush Mount Single Jack, UL
301014WH		4C White Flush Mount Dual Jack, UL
301016WH		6C White Flush Mount Dual Jack, UL
301018WH		8C White Flush Mount Dual Jack, UL
301094WH		4C White Wall Phone Jack, UL



FOR TECHNICAL SUPPORT: PHONE 973-740-40 / FAX 973-347-2111

[Back to Index](#)